



**Staccato™**  
Top-mount Kitchen Sink  
**K-3369-1**

**Features**

- Double equal bowls.
- Single faucet hole.
- Includes hardwood cutting board.
- 33" (838 mm) x 22" (559 mm)

**Material**

- 18-gauge stainless steel.

**Technology**

- Includes SilentShield® sound-absorption system.

**Installation**

- Top-mount
- Includes installation hardware.

**Optional Accessories**

K- 3194 Sink Rack  
K- 3196 Sink Rack  
K- 3370 Cutting Board  
K-8813




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**Lifetime Limited Warranty for Kohler  
Stainless Steel Sinks**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Installation: Top-mount

Cutout: Top-mount, 32-1/2" x 21-1/2" (826 mm x 546 mm) with 1" (25 mm) radius corners

Min. base cabinet width: 36" (914 mm)

Bowl area (Left)  
Length: 17-1/16" (433 mm)  
Width: 13-15/16" (354 mm)  
Bowl depth: 8-5/16" (211 mm)  
Water depth: 8" (203 mm)

Bowl area (Right)  
Length: 17-1/16" (433 mm)  
Width: 13-15/16" (354 mm)  
Bowl depth: 8-5/16" (211 mm)  
Water depth: 8" (203 mm)

Number of deck holes: 1

Faucet hole(s): 1-7/16" (37 mm)

Drain hole: 3-5/8" (92 mm)

## Notes

Install this product according to the installation guide.