KOHLER_®

Features

- Vitreous china.
- Two-piece toilet.
- Regular height Round-front bowl.
- Class Five[®] flushing system.
- Includes right-hand polished chrome trip lever.
- 2-1/8" (54 mm) fully glazed trapway.
- 14" (356 mm) rough-in.
- Less seat and supply.
- 10-1/2" (267 mm) x 7-3/4" (197 mm) water area.
- 29-5/8" (752 mm) x 18-1/4" (464 mm) x 28-3/4" (730 mm).
- Floor mount / Floor outlet.
- Insuliner[®] tank liner included.

Recommended Accessories

K- 4639 Toilet Seat K- 4689 Toilet Seat K- 7637 Angle Supply with Stop (single)

Components

Product includes: K- 4197 Round-Front Bowl K- 4841-UR Toilet Tank Additional included component/s: Tank cover, Trip lever, Bolt cap accessory pack, and Tank accessory pack.





Codes/Standards

ASME A112.19.2/CSA B45.1 DOE - Energy Policy Act 1992 EPA WaterSense®

KOHLER[®] One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description

\bigcirc	0	White

- 96 Biscuit
- 47 Almond




Wellworth® Class Five® Toilet K-3947-UR



Wellworth[®]

Class Five® Toilet K-3947-UR



Technical Information

All product dimensions are nominal.		
Toilet type:	Two-piece	
Bowl shape:	Round front	
Flush type:	Class Five	
Trap passageway:	2-1/8" (54 mm)	
Water Consumption		
Full:	1.28 gpf (4.8 lpf)	
Water surface size:	10-1/2" x 7-3/4" (267 mm x 197 mm)	
Rim to water surface:	5-1/4" (133 mm)	
Rough-in:	14" (356 mm)	
Seat-mounting holes:	5-1/2" (140 mm)	

Notes

Install this product according to the installation guide.

