

Wellworth®

Class Five® Dual Flush Toilet K-3987-RA



- Two-piece toilet.
- Round-front bowl offers an ideal solution for smaller baths and powder rooms.
- Right-hand nested trip lever offers a choice of 1.1 or 1.6 gallons per flush (gpf).
- 2-1/8-inch glazed trapway.
- Coordinates with other products in the Wellworth collection.

Technology

 Dual-flush technology allows you to choose between a full- or partial-flush.

Installation

- Standard 12-inch rough-in.
- Three-bolt installation.

Water Conservation & Rebates

- WaterSense® toilets meet strict EPA flushing guidelines, including using at least 20 percent less water than 1.6-gallon toilets.
- Eligible for consumer rebates in some municipalities.



For complete listing of available colors, go to kohler.com.



Codes/Standards

ASME A112.19.2/CSA B45.1 EPA WaterSense®

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Product Specification


Toilet shall be 27-3/4" (705 mm) in length, 18" (457 mm) in width, and 29-1/4" (743 mm) in height. Toilet shall be made of vitreous china. Toilet shall be two-piece. Product shall feature 1.6 gpf (6.1 lpf) or 1.1 gpf (4.2 lpf). Toilet shall be right-hand trip lever. Toilet shall be Class Five® dual flushing system. Toilet shall be 12" (305 mm) rough-in. Toilet shall be Kohler Model K-3987-RA.



KOHLER

Wellworth®

Class Five® Dual Flush Toilet K-3987-RA



Technical Information

All measurements are approximate only.

Toilet style: Two-piece
Bowl shape: Round front
Passageway: 2-1/8" (54 mm)
Flush rate - full: 1.6 gpf (6.1 lpf)
Flush rate - short: 1.1 gpf (4.2 lpf)

Water area: 10-1/2" x 7-3/4" (267 mm x 197 mm)

Water depth from rim: 5-1/4" (133 mm)
Rough-in: 12" (305 mm)
Seat hole centers: 5-1/2" (140 mm)

Installation Notes

Install this product according to the installation guide.

For back-to-back toilet installations: Use only a 45° double wye fitting.

