

Features

- 39-inch minimum base cabinet width.
- Extra-large/medium bowls.
- Left bowl is sized to fit a half cookie sheet flat in the bottom of the basin.
- 9-inch depth.
- No faucet holes.
- Rear drain increases workspace in the sink and allows for more storage space underneath the sink.
- SilentShield® sound-absorption technology offers quieter performance.
- Includes divider dishcloth bar, divider utility shelf, and bottom basin rack.
- Includes installation hardware.

Material

- Handcrafted from 16-gauge stainless steel.

Installation

- Under-mount.

Optional Accessories

- K- 6429 Utility Rack
- K- 6647 Sink Rack
- K- 6667 Wood Cutting Board
- K- 8801 Sink Strainer

Components

Additional included component/s: Hardware kit (3 required), Cut-out template, Divider dish cloth bar, Divider utility shelf, and Bottom bowl rackn- left.




Codes/Standards

ASME A112.19.3/CSA B45.4

Lifetime Limited Warranty for Kohler Stainless Steel Sinks

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Bowl configuration: Large/medium

Installation: Under-mount

Min. base cabinet width: 36" (914 mm)

Bowl area (Left)
Length: 20-3/4" (527 mm)
Width: 18-1/2" (470 mm)
Bowl depth: 9-5/16" (237 mm)
Water depth: 9" (229 mm)

Bowl area (Right)
Length: 11-5/8" (295 mm)
Width: 16-1/2" (419 mm)
Bowl depth: 9-5/16" (237 mm)
Water depth: 9" (229 mm)

Drain hole: 3-11/16" (94 mm)

Template: Under-mount, 1207217-7, not required, not included

Notes

Install this product according to the installation guide.

Allow a minimum of 3" (76 mm) clearance around the sink rim for clip attachment.