

- For use with Invigoration™ Series 18kW - 30kW Steam Generators.
- Fast-Response® technology produces a luxurious steam shower in 60 seconds.
- KOHLER finishes resist corrosion and tarnish.
- Quick-connect RJ-12 cord and connector.
- Mounting arm and gasket.
- Digital clock.
- Two thermostatic steam heads with aromatherapy reservoirs.
- Adjustable time and temperature settings between 90 and 125 degrees Fahrenheit.
- Controls the Power Clean feature.
- 20-minute safety shutoff.

Loose component/s: 50 ft. Data cable, Dual connector, 10" Data Cable, 72" Data Cable, 3 way Coupler, Single connector, Removal tool, and Mounting hardware.








Codes/Standards


None Applicable

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|--|------|--------------------------|
|  | CP | Polished Chrome |
|  | SN | Vibrant® Polished Nickel |
|  | BN | Vibrant® Brushed Nickel |
|  | BV | Vibrant® Brushed Bronze |
|  | 2BZ | Oil-Rubbed Bronze |



Technical Information

All product dimensions are nominal.

Notes

Install this product according to the installation guide.

CAUTION: Risk of personal injury. Do not install the User Interface Control outside the steam enclosure. The User Interface must be installed within the enclosure to allow the sensors to regulate the temperature and control the flow of steam.

CAUTION: Risk of scalding. Do not locate the steam head near a seat or bench, as the steam head is hot during operation and may scald the user if touched.

The temperature sensor should be mounted on the wall opposite the steam head. The steam head should be located as far from the seating area as possible.

Locate the steam head 6" (152 mm) above the floor and at least 4-1/2" (114 mm) from the threshold.