

Features

- Vitreous china.
- Comfort Height® elongated bowl.
- 2-1/8" fully glazed concealed trapway.
- Clean Caps low-profile bolt caps.
- 12" (305 mm) rough-in.
- Combines with the K-4434 or K-4433 tank to create a complete K-6669 or K-6999 toilet.

Recommended Accessories

- K- 7637 Angle Supply with Stop (single)
- K- 4733 Toilet Seat



Codes/Standards








ASME A112.19.2/CSA B45.1

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	NY	Dune
	95	Ice™ Grey
	G9	Sandbar
	7	Black Black™

No image available.

This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Two-piece
Bowl shape:	Elongated front
Flush type:	AquaPiston
Trap passageway:	2" (51 mm)
Water Consumption	
Full:	1.28 gpf (4.8 lpf)
Water surface size:	11" x 8" (279 mm x 203 mm)
Rim to water surface:	5-3/8" (137 mm)
Rough-in:	12" (305 mm)

Notes

Install this product according to the installation guide.