



Lawnfield®
Under-mount Offset Kitchen Sink
K-5841-4U

Features

- 36-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Large and medium size double bowl.
- Under-mount.
- Three faucet holes with one accessory hole to the left.
- 33" (838 mm) x 22" (559 mm)

Recommended Accessories

K- 9000 P-Trap

Optional Accessories

K- 6160 Sink Rack
K- 6162 Sink Rack
K- 6545 Sponge Caddy
K- 8801 Sink Strainer

Components

Additional included component/s: Under-mount sink kit 23" (584 mm).




Codes/Standards

ASME A112.19.1/CSA B45.2

KOHLER® Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Bowl configuration: Large/medium

Installation: Under-mount

Bowl area (Left) Length: 17-1/8" (435 mm)

Width: 18-5/16" (465 mm)

Bowl depth: 9" (229 mm)

Bowl area (Right) Length: 11-1/16" (281 mm)

Width: 17-5/16" (440 mm)

Bowl depth: 9" (229 mm)

Number of deck holes: 4

Faucet hole(s): 2-3/8" (60 mm)

Drain hole: 3-7/8" (98 mm)

Template: Under-mount, 1148647-7, required, included

Notes

Install this product according to the installation guide.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.