

## Features

- Metal construction.
- One-piece self-contained ceramic disc valve allows both volume and temperature control.
- Temperature memory allowing faucet to be turned on and off at any temperature setting.
- High-temperature limit stop.
- 8-1/2" (216mm) swing spout reach.
- Flexible supplies.
- Matching finish sidespray.
- Lever handle.
- 2.2 gal/min (8.3 l/min) maximum flow rate [max at 60 psi (4.14 bar)].
- Project pack six per case.

## Optional Accessories

15179-A



ADA

CSA B651

OBC

## Codes/Standards

ASME A112.18.1/CSA B125.1

NSF 61

NSF 372

DOE - Energy Policy Act 1992

ADA

ICC/ANSI A117.1


CSA B651

OBC

All applicable US Federal and State material regulations

## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Spout reach: 8-1/2" (216 mm)

## Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Pressure: 60 psi (4.1 bar)

## Notes

Install this product according to the installation guide.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.