Tanager®

Top-mount Kitchen Sink

K-6491-1

Features

- 33-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Top-mount.
- Double (equal) bowl.
- Single faucet hole.
- 33" (838 mm) x 22" (559 mm)



Recommended Accessories

K- 9000 P-Trap

Optional Accessories

K-6146
K- 6147 Sink Rack
K- 6545 Sponge Caddy
K- 8801 Sink Strainer

Codes/Standards

ASME A112.19.1/CSA B45.2


KOHLER® Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

Tanager®

Top-mount Kitchen Sink

K-6491-1



Technical Information

All product dimensions are nominal.

Bowl configuration:	Double equal
Installation:	Top-mount
Min. base cabinet width:	33" (838 mm)
Bowl area (Left)	Length: 14-5/16" (364 mm) Width: 18-3/4" (476 mm) Bowl depth: 9" (229 mm) Water depth: 9" (229 mm)
Bowl area (Right)	Length: 14-5/16" (364 mm) Width: 18-3/4" (476 mm) Bowl depth: 9" (229 mm) Water depth: 9" (229 mm)
Number of deck holes:	1
Faucet hole(s):	1-3/8" (35 mm)
Drain hole:	3-7/8" (98 mm)
Template:	Top-mount, 1066422-7, required, included

Notes

Install this product according to the installation guide.