

Features

- 15-inch minimum base cabinet width.
- KOHLER cast iron.
- Under-mount.
- Single bowl.
- Acid-resistant enamel finish.
- 12" (305 mm) x 9-1/4" (235 mm)

Recommended Accessories

K- 9000 P-Trap

Optional Accessories

K- 8801 Sink Strainer

Components

Product includes: 52047 Clamp Accessory Pack, 4 Ea.



ADA

Codes/Standards ASME A112.19.1/CSA B45.2 ADA ICC/ANSI A117.1

KOHLER[®] Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.


Color Code Description

- 0 White
- FF Sea Salt™
- 96 Biscuit
- 47 Almond
- NY Dune
- 95 Ice[™] Grey
- G9 Sandbar
- 33 Mexican Sand[™]
 - K4 Cashmere
 - FT Basalt
 - 58 Thunder™ Grey
 - 20 Suede
 - KA Black 'n Tan
 - FP Caviar
 - 7 Black Black™



Northland[™] Under-mount Bar Sink K-6589-U






Technical Information

All product dimensions are nominal.	
Bowl configuration:	Single
Installation:	Under-mount
Bowl area	Length: 12" (305 mm) Width: 9-1/4" (235 mm) Bowl depth: 7" (178 mm)
Drain hole:	3-7/8" (98 mm)
Template:	Under-mount, 1086707-7, required, included

Northland[™] Under-mount Bar Sink K-6589-U



Wood Counter Installation

Note: Waterproof the unprotected overhang area on the underside of a wood counter.

Notes

Install this product according to the installation guide.

Supplied bowl clamp assemblies require 1" (25 mm) minimum countertop thickness. Installer must supply anchors for thinner countertops.

For multiple bowl under-mount installations, a minimum distance of 3-3/8" (86 mm) is required between bowls. Countertop supplier to determine required support.

ADA compliant when installed to the specific requirements of these regulations.

