

### Features

- 25-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Top-mount.
- Three faucet holes.
- 25" (635 mm) x 22" (559 mm)

## **Recommended Accessories**

K- 9000 P-Trap

### **Optional Accessories**

- K- 6194 Utility Rack with Soaking Cup
- K- 6239 Colander with Cutting Board
- K- 6246 Cutting Board
- K- 8801 Sink Strainer

## Components

Product includes: K- 6238 Sink Rack 1054375 Under-mount Sink Kit, 23"



Codes/Standards ASME A112.19.1/CSA B45.2

# KOHLER<sup>®</sup> Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

## Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
$\bigcirc$	0	White
$\bigcirc$	FF	Sea Salt™
$\bigcirc$	96	Biscuit
$\bigcirc$	47	Almond
$\bigcirc$	FD	Cane Sugar™
$\bigcirc$	95	Ice™ Grey
	G9	Sandbar

- K4 Cashmere
  - 20 Suede
  - KA Black 'n Tan
  - 7 Black Black™




# Riverby® Top-mount Kitchen Sink K-5872-3A1



4-5/16"

(110 mm)



## **Technical Information**

All product dimensions are nominal.		
Bowl configuration:	Single	
Installation:	Top-mount	
Bowl area (Only)	Length: 22-1/4" (565 mm) Width: 15-13/16" (402 mm) Bowl depth: 9" (229 mm)	
Number of deck holes:	3	
Faucet hole(s):	1-3/8" (35 mm)	
Drain hole:	3-7/8" (98 mm)	
Template:	Top-mount, 1172565-7, required, included	

### Notes

Install this product according to the installation guide.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4-KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used.

IMPORTANT! Use of the colander, wood cutting board, and utility rack requires the "reveal" cutout option on the cutout template.

