

Addison™ Top-mount Bar Sink K-6552

### **Features**

- 15-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Top-mount.
- Single compartment.
- 13" (330 mm) x 13" (330 mm).

# **Recommended Accessories**

K- 9000 P-Trap

# **Optional Accessories**

K-8801 Sink Strainer



ADA

## Codes/Standards

ASME A112.19.1/CSA B45.2 ADA ICC/ANSI A117.1

# **KOHLER® Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty**


See website for detailed warranty information.

## **Available Color/Finishes**

Color tiles intended for reference only.


Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	7	Black Black™







Top-mount Bar Sink K-6552



## **Technical Information**

All product dimensions are nominal.

Bowl configuration: Single Installation: Top-mount

Cutout: Top-mount, 11-3/4" x 11-3/4" (298 mm x

298 mm) with 1" (25 mm) radius corners

Bowl area Length: 10" (254 mm)

Width: 10" (254 mm)

Bowl depth: 6" (152 mm)

Drain hole: 3-5/8" (92 mm)

#### **Notes**

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.

