

Features

- Semi-frameless, 3/8-inch-thick Crystal Clear tempered glass.
- 3/8" (10 mm) tempered glass sidelite.
- Sliding transom.
- Contemporary inside and outside solid 12-inch handles complete the look of this door.
- CleanCoat® technology creates a barrier between the water and glass to help keep your shower door looking new.

Material

- Anodized aluminum prevents rusting or corrosion.
- Tempered glass ensures maximum safety and durability.

Installation

- Out-of-plumb adjustability allows for simpler installation.
- Can be installed to open to the left or right.

Components

Additional included component/s: Hardware kit, and steam-sealing kit.



Codes/Standards

CPSC 16CFR 1201
ANSI Z97.1 (Tempered Glass)


KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	SH	Bright Silver
	NX	Brushed Nickel
	ABV	Anodized Brushed Bronze
	BNK	Anodized Brushed Nickel



Technical Information

All product dimensions are nominal.

Installation type: For receptor installation

Opening style: Pivot

Opening Width - Min: 57" (1448 mm)

Opening Width - Max: 60" (1524 mm)

Walk-through - Min: 28-7/16" (722 mm)

Walk-through - Max: 31-7/16" (799 mm)

Glass thickness: 3/8" (10 mm)

Steam capable: YES

Notes

Install this product according to the installation guide.

Recommended two person installation.