



## Langlade® Smart Divide®

Top-mount Kitchen Sink

**K-6626-5**

### Features

- 33-inch minimum base cabinet width.
- KOHLER cast iron.
- Acid-resistant enamel finish.
- Double (equal) compartment.
- Top-mount.
- Smart Divide™ lowered divider.
- Three faucet holes with one accessory hole to the right and one accessory hole to the left.
- 33" (838 mm) x 22" (559 mm).

### Recommended Accessories

K- 9000 P-Trap

### Optional Accessories

K- 6061 Sink Rack  
K- 6066 Sink Rack  
K- 6545 Sponge Caddy  
K- 8801 Sink Strainer



### Codes/Standards












ASME A112.19.1/CSA B45.2

### KOHLER® Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

### Available Color/Finishes

*Color tiles intended for reference only.*

| Color  | Code | Description  |
|--|------|--------------|
|  | 0    | White        |
|  | FF   | Sea Salt™    |
|  | 96   | Biscuit      |
|  | 47   | Almond       |
|  | FD   | Cane Sugar™  |
|  | 95   | Ice™ Grey    |
|  | G9   | Sandbar      |
|  | K4   | Cashmere     |
|  | 20   | Suede        |
|  | KA   | Black 'n Tan |
|  | 7    | Black Black™ |

USA/Canada: 1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com).

4-13-2016 02:15


THE BOLD LOOK  
OF **KOHLER**®



## Langlade® Smart Divide®

Top-mount Kitchen Sink

**K-6626-5**



### Technical Information

All product dimensions are nominal.

Bowl configuration: Double equal

Installation: Top-mount

Bowl area (Left) Length: 15" (381 mm)  
Width: 18-3/8" (467 mm)  
Bowl depth: 9" (229 mm)

Bowl area (Right) Length: 15" (381 mm)  
Width: 18-3/8" (467 mm)  
Bowl depth: 9" (229 mm)

Number of deck holes: 5

Faucet hole(s): 1-3/8" (35 mm)

Drain hole: 3-5/8" (92 mm)

Template: Top-mount, 1043753-7, required, included

### Notes

Install this product according to the installation guide.