



Riverby®
Under-mount Kitchen Sink
K-8669-5UA3

Features

- 36-inch minimum base cabinet width.
- Offset double bowl.
- Three oversized faucet holes with one oversized accessory hole to the right and one oversized accessory hole to the left.
- 9 inch depth.
- Includes cutout templates.

Material

- KOHLER enameled cast iron.

Installation

- Under-mount.

Recommended Accessories

K- 9000 P-Trap

Optional Accessories

K- 8801 Sink Strainer

Components

Product includes:

- K- 6239 Colander with Cutting Board
- K- 9234 Stainless Steel Sink Rack
- K- 6194 Utility Rack with Soaking Cup



Codes/Standards













ASME A112.19.1/CSA B45.2

KOHLER® Enameled Cast Iron Kitchen Sink - Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	FF	Sea Salt™
	96	Biscuit
	47	Almond
	FD	Cane Sugar™
	NY	Dune
	95	Ice™ Grey
	G9	Sandbar
	33	Mexican Sand™
	K4	Cashmere
	FT	Basalt
	58	Thunder™ Grey
	20	Suede
	KA	Black 'n Tan
	FP	Caviar
	7	Black Black™


USA/Canada: 1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com.

3-27-2016 05:36

THE BOLD LOOK
OF **KOHLER®**



Technical Information

All product dimensions are nominal.

Bowl area (Left)	Length: 17-9/16" (446 mm)
	Width: 17-1/4" (438 mm)
	Bowl depth: 9" (229 mm)
	Water depth: 9" (229 mm)
Bowl area (Right)	Length: 11-1/16" (281 mm)
	Width: 17-1/4" (438 mm)
	Bowl depth: 9" (229 mm)
	Water depth: 9" (229 mm)

Number of deck holes: 5

Template: Under-mount, 1166727-7, required, included

Notes

Install this product according to the installation guide.