

Artifacts[™] Gentleman's[™]

Bar Faucet K-99268

Features

- The vintage artisan inspired top-mount handle provides a unique statement to any kitchen.
- Ceramic disc valves exceed industry longevity standards, ensuring durable performance for life.
- Single lever handle is simple to use and makes adjusting water temperature easy.
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage.
- 1.8 gallons (6.8 L) per minute maximum flow rate at 60 psi (4.1 bar).
- Meets CalGreen requirements for kitchen faucets.

Material

• Premium metal construction.

Installation

- Flexible connections for easy installation.
- Single-hole installation.

Adapters, Rough-in and Extension Kits

1012715 Range: 3-1/4" (83 mm) - 5-3/8" (137 mm)

Recommended Accessories

1054432 1.5gpm (5.7 l/min) Aerator Kit



Codes/Standards

ASME A112.18.1/CSA B125.1 NSF 61 NSF 372 DOE - Energy Policy Act 1992 All applicable US Federal and State material regulations

KOHLER[®] Faucet Lifetime Limited Warrantv

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description

CP	Polished Chrome	


- SN Vibrant® Polished Nickel
- VS Vibrant® Stainless
- 2BZ Oil-Rubbed Bronze



KOHLER, Faucets

Artifacts[™] Gentleman's[™]

Bar Faucet **K-99268**



Technical Information

All product dimensions are nominal. Valve body: Plastic Spout reach: 7-5/16" (186 mm) Faucet: Flow rate: 1.8 gal/min (6.8 l/min)

Flow rate:1.8 gal/min (6.8 l/miPressure:60 psi (4.1 bar)

Notes Install this product according to the installation guide.

