

Date: 5/2/2016

Position | Count | Description

1 UP 10-16 A PM B5/LC



Product photo could vary from the actual product

Product No.: 98420222

The high-efficiency Grundfos Comfort PM range is a product for domestic hotwater re-circulation with lead free drinking water suitable pump housing for single- and two-family houses powered by a high efficiency single-phase, 12-pole, permanent-magnet motor.

Features and benefits:

- * Quick and simple electrical installation due to the highly reliable ALPHA plug
- * dry running detection
- * Easy-to-clean and lime-insensitive spheric rotor
- * Wearless operation due to liquid lubricated bearing
- * No leakage risk due to a static seal
- * Easy maintenance and cleaning through the easy-to-separate pump head fitting almost all competitor pump housings
- * Corrosion resistant lead free brass pump housing
- * No additional motor protection necessary due to integrated motor electronics

Liquid:

Pumped liquid: Water
Liquid temperature range: 35.6 .. 203 °F
Liquid temp: 140 °F
Density: 61.35 lb/ft³

Technical:

TF class: 95
Approvals on nameplate: UL,CSA

Materials:

Pump housing: Brass MS 68

Impeller: Stainless steel, EPDM, PPO, PTFE, Graphit

Installation:

Maximum operating pressure: 145 psi
Flange standard: USA Sweat
Pipe connection: 1/2" Sweat
Pressure stage: 10
Port-to-port length: 3 1/8 in

Electrical data:

 $\begin{array}{ll} \text{C run:} & 0.6 \ \mu\text{F} \\ \text{Max. power input:} & 6 \ \text{W} \\ \text{Main frequency:} & 60 \ \text{Hz} \end{array}$




Date: 5/2/2016

			Date.	3/2/2010
Position	Count	Description		
			1 x 115-230 V	
		Rated voltage:	1 X 113-230 V	
		Current in speed 3:	0,10/0,07 A	
		Capacitor size - run:	0.6 μF	
		Enclosure class (IEC 34-5):	IP44	
		Insulation class (IEC 85):	F	
		Cable type:	Connecting cord with plug	
		Type of cable plug:	NEMA 5-15P	
		Others:		
		Shipping volume:	0.12 ft ³	
		- Tripping retained		



Date: 5/2/2016


98420222 UP 10-16 A PM B5/LC 60 Hz








Date: 5/2/2016

Description	Value	
General information:		
Product name:	UP 10-16 A PM B5/LC	
Product No.:	98420222	
EAN:	5711494712878	
Price:	On request	
Technical:		
Speed Number:	1	
Head max:	5.25 ft	
TF class:	95	
Approvals on nameplate:	UL,CSA	
Materials:		
Pump housing:	Brass MS 68	
Impeller:	Stainless steel, EPDM, PPO PTFE, Graphit	
Installation:		
Maximum operating pressure:	145 psi	
Flange standard:	USA Sweat	
Pipe connection:	1/2" Sweat	
Pressure stage:	10	
Port-to-port length:	3 1/8 in	









0.12 ft³

Water

35.6 .. 203 °F

Pumped liquid:

Shipping volume:


Liquid temperature range:






Date: 5/2/2016

98420222 UP 10-16 A PM B5/LC 60 Hz






Note! All units are in [mm] unless otherwise stated. Disclaimer: This simplified dimensional drawing does not show all details.



Date: 5/2/2016

98420222 UP 10-16 A PM B5/LC 60 Hz



All units are [mm] unless otherwise presented.