




# PRESSURE BALANCE BATH/SHOWER FITTING WITH WATER-SAVING SHOWERHEAD



T722.508 Bath/Shower Trim Shown

### **GENERAL DESCRIPTION:**

### **SHOWERHEAD**

Water saving 3-function showerhead. At maximum 1.75 gpm/6.61 L/min. flow rate.

#### **WALL TUB SPOUT**

Metal slip-on diverter spout.

### **WALL VALVE TRIM**

Metal lever handle. Metal wall escutcheon.


- Coordinates with Estate<sup>®</sup> Suite of fixtures.
- Available Exclusively at Ferguson® Showrooms.

## **MODEL NUMBER:**

# TRIM KITS:

- ☐ T722.508 Estate BATH/SHOWER Trim Kit
  Lever handle. Water-saving showerhead. LESS valve body.
- ☐ T722.507 Estate SHOWER ONLY Trim Kit
  Lever handle. Water-saving showerhead. LESS valve body.

For use with R110 Series Pressure Balance Valves. See reverse side for available Rough Valves.



# SUGGESTED SPECIFICATION

Bath/shower fitting shall feature water saving 3-function showerhead with Max. 1.75 gpm/6.61 L/min. flow rate. Fitting shall be: American Standard - Trim Kit Model # T722.50\_.\_\_\_ and Valve Body Model # R11\_.

© 2016 AS America, Inc.




# **ESTATE®**

# PRESSURE BALANCE BATH/SHOWER FITTING WITH WATER-SAVING SHOWERHEAD

# **CODES AND STANDARDS**

These products meet or exceed the following codes and standards:

ANSI A117.1 ASSE 1016 ASME A112.18.1 CSA B125.1



		* TRIM & ROUGH MUST BE ORDERED SEPARATELY.	Finish Options			
* •	Product		Polished Chrome	PVD Polished Nickel	Legacy Bronze	PVD Satin Nickel
X	Number	Description	002	013	013	295
TRIM	T722.508	Bath/Shower Trim Kit. Metal lever handle. Water-Saving showerhead. LESS valve body.				
	T722.507	Shower Only Trim Kit. Metal lever handle. Water-saving showerhead. LESS valve body.				

	Product Number	Description
	R111	Rough Valve Body less trim. Universal inlets/outlets.
	R111SS	Rough Valve Body less trim. Universal inlets/outlets with Screwdriver Stops.
	R110	Rough Valve Body less trim. Direct sweat inlets/outlets.
ПОО	R110SS	Rough Valve Body less trim. Direct sweat inlets/outlets with Screwdriver Stops.
m	R115	Rough Valve Body less trim. Female Thread inlets/outlets.
LVE	R115SS	Rough Valve Body less trim. Female Thread inlets/outlets with Screwdriver Stops.
	R117	Rough Valve Body less trim. PEX inlets/universal outlets for Crimp Ring PEX system (ASTM F1807).
ROUGH	R117SS	Rough Valve Body less trim. PEX inlets/universal outlets for Crimp Ring PEX system (ASTM F1807) with Screwdriver Stops.
8	R118	Rough Valve Body less trim. PEX inlets/universal outlets for Cold Expansion PEX system (ASTM F1960).
	R118SS	Rough Valve Body less trim. PEX inlets/universal outlets for Cold Expansion PEX system (ASTM F1960) with Screwdriver Stops.
	R119	Rough Valve Body less trim. CPVC inlets/universal outlets.
	R119SS	Rough Valve Body less trim. CPVC inlets/universal outlets with Screwdriver Stops.

Meets the American Disabilities Act Guidelines and ANSI A117.1 Requirements for the physically challenged.

PART OF LIXIL

© 2016 AS America, Inc.