



# Levity®

## Frameless Sliding Shower Door

### K-706011-L

#### Features

- Frameless design highlights showering area.
- Innovative roller design simplifies installation and provides out-of-plumb adjustability.
- Frameless, 3/8" (10 mm) thick frosted Crystal Clear glass.
- Door tracking system features a hidden, cushioned, center guide for smooth, quiet sliding action.
- Smooth, easy-to-clean wall jambs.
- Contemporary vertical blade handles complete the look of this door.
- CleanCoat® technology creates a barrier between the water and glass to help keep your shower door looking new.

#### Material

- Anodized aluminum prevents rusting or corrosion.
- Tempered glass ensures maximum safety and durability.

#### Installation

- Out-of-plumb adjustability allows for simpler installation.
- Can be installed to open to the left or right.

#### Components

Additional included component/s: Hardware kit.



#### Codes/Standards




CPSC 16CFR 1201  
ANSI Z97.1 (Tempered Glass)



#### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

#### Available Color/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	SHP	Bright Polished Silver
	NX	Brushed Nickel
	ABV	Anodized Brushed Bronze



**\* Walk-through**

## Technical Information

All product dimensions are nominal.

Installation type: For receptor installation

Opening style: Sliding/Bypass

Opening Width - Min:  $44\frac{5}{8}"$  (1133 mm)

Opening Width - Max:  $47\frac{5}{8}"$  (1210 mm)

Walk-through - Min:  $18\frac{1}{16}"$  (459 mm)

Walk-through - Max:  $21\frac{1}{16}"$  (535 mm)

Glass thickness:  $\frac{3}{8}"$  (10 mm)

## Notes

Install this product according to the installation guide.

If replacing a shower door, the narrow wall jamb design of this door may not cover the existing shower door holes.