

Levity[®] Frameless Sliding Shower Door K-706012-L

Features

- Frameless design highlights showering area.
- Innovative roller design simplifies installation and provides out-of-plumb adjustability.
- Frameless, 3/8" (10 mm) thick frosted Crystal Clear glass.
- Door tracking system features a hidden, cushioned, center guide for smooth, quiet sliding action.
- Smooth, easy-to-clean wall jambs.
- Contemporary vertical blade handles complete the look of this door.
- CleanCoat[®] technology creates a barrier between the water and glass to help keep your shower door looking new.

Material

- Anodized aluminum prevents rusting or corrosion.
- Tempered glass ensures maximum safety and durability.

Installation

- Out-of-plumb adjustability allows for simpler installation.
- Can be installed to open to the left or right.

Components

Additional included component/s: Hardware kit.



Codes/Standards

CPSC 16CFR 1201 ANSI Z97.1 (Tempered Glass)

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description

\bigcirc	SHP	Bright Polished Silver
	NX	Brushed Nickel


- NX Brushed Nickel
- ABV Anodized Brushed Bronze



Levity®

KOHLER_®

Frameless Sliding Shower Door K-706012-L



Technical Information

All product dimensions are nominal.

Installation type:For receptor installationOpening style:Sliding/BypassOpening Width - Min:56-5/8" (1438 mm)Opening Width - Max:59-5/8" (1514 mm)Walk-through - Min:24-9/16" (624 mm)Walk-through - Max:27-9/16" (700 mm)Glass thickness:3/8" (10 mm)

Notes

Install this product according to the installation guide.

If replacing a shower door, the narrow wall jamb design of this door may not cover the existing shower door holes.

