

Features

- Brass construction.
- Brass valve bodies.
- Quarter-turn washerless ceramic disc valves.
- Less drain.
- Lower flow aerator options are available (refer to the Kohler Price Book).
- Variety of handle style options.
- Handspray.
- For 8" (203 mm) centers.
- 8-1/8" (206 mm) swing spout.
- 2.0 gal/min (7.6 l/min) maximum flow rate [max at 60 psi (4.14 bar)].

Required Accessories

- K- 16012-2 Standard Handles for Widespread Base Faucet
- or
- K- 16012-3 Cross Handles for Widespread Base Faucet
- or
- K- 16012-4 Lever Handles for Widespread Base Faucet
- or
- K- 16012-5 Wristblade Handles for Widespread Base Faucet

Optional Accessories

- 77619 Deep Rough-in Kit
- 1011402 SD Spray Deep Rough-in Kit
- 1160595 .35 gpm Aerator, Medium




ADA

Codes/Standards

NSF 61
NSF 372
DOE - Energy Policy Act 1992
ADA
ICC/ANSI A117.1

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Spout reach: 8-1/8" (206 mm)

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.