


Clear Vinyl Tubing

Product Features

- Crystal clear clarity
 - Good flexibility
 - Smooth, dense bore maximizes flow and reduces sediment build up.
 - Resistance to acids, alkalis and many solvents.
 - Typical applications: Beverage dispensing, potable water, drainage lines, aquarium tubing, laboratory tubing, protective insulation.
 - Material: polyvinyl chloride
- Maximum operating temperature: 175° F
 Pressure Range: 19 to 55 psi (131-379 kPa)
 Brittle Point: -40°F (-40°C)
 Hardness: Durometer 83+/-3 Shore A
 Toxicity: Non-toxic FDA listed material



PF149012N

Notes

PROFLO vinyl tubing is not recommended for esters, ketones and some aromatics. PROFLO vinyl tubing should not be used for repairs or installation of dishwasher supply or discharge lines or on ice maker applications.

Specifications Chart

| | I.D. | | O.D. | | Wall | | Length | | Working PSI |
|-----------|------|--------|-------|---------|------|-------|--------|-------|-------------|
| | in | mm | in | mm | in | mm | ft. | m | at 70° F |
| PF149012N | 1/8 | 3.175 | 1/4 | 6.350 | 1/16 | 1.588 | 100 | 30.48 | 55 |
| PF149014N | 3/16 | 4.763 | 5/16 | 7.938 | 1/16 | 1.588 | 100 | 30.48 | 55 |
| PF149016N | 1/4 | 6.350 | 3/8 | 9.525 | 1/16 | 1.588 | 100 | 30.48 | 55 |
| PF149022N | 3/8 | 9.525 | 1/2 | 12.700 | 1/16 | 1.588 | 100 | 30.48 | 45 |
| PF149026N | 1/2 | 12.700 | 5/8 | 15.875 | 1/16 | 1.588 | 100 | 30.48 | 45 |
| PF149028N | 1/2 | 12.700 | 3/4 | 19.050 | 1/8 | 3.175 | 100 | 30.48 | 55 |
| PF149030N | 5/8 | 15.875 | 7/8 | 22.225 | 1/8 | 3.175 | 100 | 30.48 | 40 |
| PF149032N | 3/4 | 19.050 | 1 | 25.400 | 1/8 | 3.175 | 50 | 15.24 | 35 |
| PF149034N | 1 | 25.400 | 1-1/4 | 31.7500 | 1/8 | 3.175 | 50 | 15.24 | 25 |

Warranty and Codes

This PROFLO product carries a 1-year limited warranty.

