


FIGURE 7010E - Adjustable Swivel Ring Hangers



UL Approved - Sizes 1/2" to 8"
 FM Approved - Sizes 3/4" to 8"

Finish: Epoxy Plated
 Color: Zinc
 MSS SP-58, Type 10
 Federal Specification WW-H-171, Type 10
 NFPA 13



A - Rod size (hanger rod not included)
 B - Center of pipe to top of knured hanger rod nut
 C - Rod take out (center of pipe to bottom of hanger rod
 D - Top of pipe to bottom of hanger rod nut


Catalog Number	Pipe Size		A (Rod size)	B		C		D		Design Load		Weight Lbs.
	in.	mm		in.	mm	in.	mm	in.	mm	Lbs.	kN	
FNW7010EP0050	1/2	21.3	3/8-16UNC	2-7/32	56.36	25/32	19.8	7/8	22.2	300	1.33	0.09
FNW7010EP0075	3/4	26.7	3/8-16UNC	2-7/16	61.91	1-1/32	26.2	1-3/32	27.8	300	1.33	0.09
FNW7010EP0100	1	33.4	3/8-16UNC	2-5/8	66.68	1-7/32	31.0	1-3/16	30.2	300	1.33	0.10
FNW7010EP0125	1-1/4	42.2	3/8-16UNC	2-25/32	70.64	1-3/8	34.9	1-5/32	29.4	300	1.33	0.11
FNW7010EP0150	1-1/2	48.3	3/8-16UNC	2-7/8	73.03	1-7/16	36.5	1-3/32	27.8	300	1.33	0.12
FNW7010EP0200	2	60.3	3/8-16UNC	3-1/32	76.99	1-19/32	40.5	1-1/32	26.2	300	1.33	0.13
FNW7010EP0250	2-1/2	73	3/8-16UNC	3-31/32	100.81	2-9/16	65.1	1-23/32	43.7	525	4.45	0.29
FNW7010EP0300	3	88.9	3/8-16UNC	4-15/32	113.51	3-1/16	77.8	1-15/16	49.2	525	4.45	0.33
FNW7010EP0350	3-1/2	101.6	3/8-16UNC	4-15/16	125.41	3-17/32	89.7	2-1/8	54.0	585	4.45	0.37
FNW7010EP0400	4	114.3	3/8-16UNC	5-9/32	134.14	3-27/32	97.6	2-3/16	55.6	650	4.89	0.39
FNW7010EP0500	5	141.3	1/2-13UNC	5-31/32	151.61	4-7/16	112.7	2-1/4	57.2	1000	4.89	0.53
FNW7010EP0600	6	168.3	1/2-13UNC	7	177.80	5-1/2	139.7	2-3/4	69.9	1000	5.56	0.72
FNW7010EP0800	8	219.1	1/2-13UNC	7-31/32	202.41	6-7/16	163.5	2-23/32	69.1	1000	5.56	1.04

FIGURE 7010Z - Adjustable Swivel Ring Hangers



FM Approved - Sizes 3/4" to 8"
 UL Approved - Sizes 1/2" to 8"

Finish: Plated
 Color: Zinc
 MSS SP-58, Type 10
 Federal Specification WW-H-171, Type 10
 NFPA 13



A - Rod size (hanger rod not included)
 B - Center of pipe to top of knured hanger rod nut
 C - Rod take out (center of pipe to bottom of hanger rod
 D - Top of pipe to bottom of hanger rod nut

Catalog Number	Pipe Size		A (Rod size)	B		C		D		Design Load		Weight Lbs.
	in.	mm		in.	mm	in.	mm	in.	mm	Lbs.	kN	
FNW7010Z0050	1/2	21.3	3/8	2.32	59	1.34	34	1.06	27	500	2.220	0.09
FNW7010Z0075	3/4	26.7	3/8	2.56	65	1.57	40	1.18	30	500	2.220	0.09
FNW7010Z0100	1	33.4	3/8	2.64	67	1.65	42	1.14	29	500	2.220	0.10
FNW7010Z0125	1-1/4	42.2	3/8	2.72	69	1.73	44	1.06	27	500	2.220	0.10
FNW7010Z0150	1-1/2	48.3	3/8	2.87	73	1.89	48	1.10	28	500	2.220	0.11
FNW7010Z0200	2	60.3	3/8	3.07	78	2.08	53	1.06	27	500	2.220	0.12
FNW7010Z0250	2-1/2	73	3/8	3.39	86	2.40	61	1.06	27	1000	4.440	0.26
FNW7010Z0300	3	88.9	3/8	3.90	99	2.91	74	1.30	33	1000	4.440	0.29
FNW7010Z0350	3-1/2	101.6	3/8	4.09	104	3.11	79	1.26	32	1000	4.440	0.32
FNW7010Z0400	4	114.3	3/8	4.60	117	3.62	92	1.50	38	1000	4.440	0.35
FNW7010Z0500	5	141.3	1/2	5.43	138	4.17	106	1.57	40	1900	8.450	0.52
FNW7010Z0600	6	168.3	1/2	6.34	161	5.08	129	1.97	50	1900	8.450	0.61
FNW7010Z0800	8	219.1	1/2	7.99	203	6.73	171	2.63	67	1900	8.450	0.77