


FIGURE 7022Z - Riser Clamps



UL Approved - Sizes 1/2" to 8"


Finish: Plated
 Color: Zinc
 MSS SP-58, Type 8
 Federal Specification WW-H-171, Type 8



Catalog Number	Pipe Size		L		Bolt Size	Design Load		Torque Value	Weight
	in.	mm	in.	mm		Lbs.	kN		
FNW7022Z0050	1/2	21.3	8.50	216	3/8 x 30	220	0.98	33~45	1.03
FNW7022Z0075	3/4	26.7	8.78	223	3/8 x 30	220	0.98	33~45	1.07
FNW7022Z0100	1	33.4	9.02	229	3/8 x 30	220	0.98	33~45	1.11
FNW7022Z0125	1-1/4	42.2	9.45	240	3/8 x 30	250	1.12	33~45	1.17
FNW7022Z0150	1-1/2	48.3	9.84	250	3/8 x 30	250	1.12	33~45	1.21
FNW7022Z0200	2	60.3	10.23	260	3/8 x 30	300	1.34	33~45	1.50
FNW7022Z0250	2-1/2	73	11.02	280	3/8 x 30	400	1.78	33~45	2.10
FNW7022Z0300	3	88.9	11.81	300	3/8 x 30	500	2.23	33~45	2.23
FNW7022Z0400	4	114.3	12.99	330	1/2 x 40	750	3.34	58~78	3.45
FNW7022Z0500	5	141.3	14.48	368	1/2 x 40	1500	6.68	58~78	3.90
FNW7022Z0600	6	168.3	15.98	406	1/2 x 40	1600	7.12	58~78	4.33
FNW7022Z0800	8	219.1	18.27	464	5/8 x 50	2500	11.2	145~193	9.95
FNW7022Z1000	10	273	20.63	524	5/8 x 50	2500	11.2	145~193	11.48
FNW7022Z1200	12	323.8	22.44	570	5/8 x 50	2700	12	145~193	16.53

FIGURE 7022S - Riser Clamps

Finish: 304 Stainless Steel
 MSS SP-58, Type 1
 Federal Specification WW-H-171, Type 1
 riser clamp body : ASTM A240
 bolt , nut : SS304



Catalog Number	Pipe Size		L		Bolt Size	Design Load		Torque Value	Weight
	in.	mm	in.	mm		Lbs.	kN		
FNW7022S0050	1/2	21.3	8-1/2	215.9	3/8-16UNC	220	0.98	25 ft.lbs	0.65
FNW7022S0075	3/4	26.7	9	228.5	3/8-16UNC	220	0.98	25 ft.lbs	0.71
FNW7022S0100	1	33.4	9-1/16	230	3/8-16UNC	220	0.98	25 ft.lbs	0.73
FNW7022S0125	1-1/4	42.2	9-1/2	241.3	3/8-16UNC	250	1.11	25 ft.lbs	0.77
FNW7022S0150	1-1/2	48.3	9-9/10	251.5	3/8-16UNC	250	1.11	25 ft.lbs	0.81
FNW7022S0200	2	60.3	10-3/10	261.6	3/8-16UNC	250	1.33	25 ft.lbs	1.44
FNW7022S0250	2-1/2	73	11-1/16	281	3/8-16UNC	300	1.78	25 ft.lbs	1.56
FNW7022S0300	3	88.9	11-3/4	298.5	3/8-16UNC	400	2.22	25 ft.lbs	1.79
FNW7022S0400	4	114.3	12-15/16	328.6	1/2-13UNC	500	3.33	55 ft.lbs	3.05
FNW7022S0500	5	141.3	14-1/4	362	1/2-13UNC	750	6.67	55 ft.lbs	3.41
FNW7022S0600	6	168.3	15-1/2	393.7	1/2-13UNC	1500	7.11	55 ft.lbs	4.78
FNW7022S0800	8	219.1	18-1/4	463.5	5/8-11UNC	1600	11.12	80 ft.lbs	9.23
FNW7022S1000	10	273	20-1/10	510.5	5/8-11UNC	2500	11.12	80 ft.lbs	10.39
FNW7022S1200	12	323.8	22-3/8	568.3	5/8-11UNC	2700	12.01	80 ft.lbs	16.09