For Residential and Light Commercial Applications

Job Name	Contractor
lob Logation	Approval
Job Location	Approval
Engineer	Contractor's P.O. No.
Approval	Representative

Plastic Filter Housings

Top Quality and Economical Plastic Filter Housings

Single Cartridge Filter Housings Sizes: 1/4" – 11/2" (6 – 40mm)

Our poly filter housings are manufactured from the highest quality, FDA grade, 100% polypropylene and acrylic styrene (for clear housings). Leak-proof sealing is accomplished by compression against a top seated EPDM O-ring located in the housing's sump. Thick wall and added ribs make the housings ideal for a wide range of applications. Polypropylene construction provides excellent chemical resistance in most installations environments. Housings supplied with and without pressure relief valves. See specifications table for pressure and temperature ratings.

Full product line

We offer a complete line of poly filter housings for virtually every application where single cartridge housings are typically used. Select from standard, heavy-duty, full-flow, high-purity, high-temp and valve-in-head models.

Features

- Full product line for more types, models, pipe fittings and options
- Heavy-duty construction, made using high-quality FDA grade polypropylene
- Superior chemical resistance from many aggressive chemicals
- Buttress thread design for superior security
- Thick side walls with heavy-duty ribs to provide greater strength
- Temperature rated to 125°F (52°C)
- Cap, sump and top-seated O-rings compress to provide leak proof sealing

See specifications table for more details.

NOTICE


The information contained herein is not intended to replace the full product installation and safety information available or the experience of a trained product installer. You are required to thoroughly read all installation instructions and product safety information before beginning the installation of this product.

PURE WATER
















A WARNING

Do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.




Dimensions





HOUSING TYPE	SIZE			DIMENSIONS											
			A B		3	С		D		F		G		Н	
	in.	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm
Blue/Black/Clear	10	4.72	120	1.57	40	1.18	30	1.18	30	10.5	267	11.0	279	11.8	300
Blue/Black/Clear	20	4.72	120	1.57	40	1.18	30	1.18	30	20.47	520	21.26	540	22.8	579
High Temp	10	5.35	136	2.22	56	2.28	58	0.23	6	10.43	265	11.49	292	12.5	318
High Temp	20	5.35	136	2.22	56	2.28	58	0.23	6	20.47	520	21.26	540	22.8	579
Full Flow (FF)	10	7.28	186	3.03	77	3.03	77	0.275	7	11.33	288	11.57	294	14.0	356
Full Flow (FF)	20	7.28	186	3.03	77	3.03	77	0.275	7	21.25	540	21.65	550	24.0	25







High Temp (10" and 20")



Blue/Black (10" and 20")



(10" and 20")

Specifications

Material: sumps & caps	FDA grade polypropylene.
Material: 0-rings	EPDM is standard; Viton is available as a spare part.
Maximum temperature (standard)	125°F (52°C)
Maximum temperature (high temp)	200°F (93°C)
Minimum temperature	40°F (4°C)
Maximum pressure (standard)	125psi (8.75 bar)
Maximum pressure (full flow)	90psi (6.3 bar)



PWHIB10BB - PWHIB10FF

Individually Boxed Plastic Housings in Master Cartons

MODEL NO.	ORDERING CODE	SIZE	PIPE	TYPE	SUMP	CAP	CASE QTY.
PWHIB34VIH	7100267	10"	3/4"	Valve-In-Head	Clear	White	4
PWHIB10FF	7100268	10"	1"	Full Flow (FF)	Blue	Black	4
PWHIB10FFCL	7100516	10"	1"	Full Flow (FF)	Clear	Black	4
PWHIB20FF	7100269	20"	1"	Full Flow (FF)	Blue	Black	4

^{*}Complete with housing, wrench, bracket and mounting screws

Poly Filter Housing

ORDERING CODE	SIZE	PIPE	SUMP	CAP	# CASE			
7100589	5"	1/3"	White	White	12			
7100303	<u> </u>	/2	Willia	Willo	12			
		1 4/11	T 21	1 1				
		· ·	 		4			
					4			
					4			
					4			
					4			
			-		4			
					4			
	20"	1"	Clear	Black PR	4			
Housings								
7100276	10"	1/4"	Blue	Black	4			
7100277	10"	1/4"	Blue	Black PR	4			
7100278	10"	1/2"	Blue	Black	4			
7100279	10"	1/2"	Blue	Black PR	4			
7100280	10"	3/4"	Blue	Black	4			
7100281	10"	3/4"	Blue	Black PR	4			
				<u>, </u>				
	20"	14"	Rluo	Block	6			
					6			
	20	/2	Diue	DIACK PN	0			
usings								
7100286	10"	3/4"	Blue	Black PR	4			
7100287	10"	•	Blue	Black	4			
7100288	10"		Blue	Black PR	4			
7100289	10"		Blue	Black	4			
7100290	10"	1½"	Blue	Black PR	4			
usings								
	20"	3/4"	Blue	Black PR	4			
l		1"	-		4			
		1"	-		4			
		· ·		+	4			
		· ·			4			
			Dido	DidokTTT				
					4			
		*			4			
ets - incluc	des hous	sing mour	nting scre	ews				
7300605		1						
7100463		1						
7100464	[1						
7100465		1						
 								
t		1						
		1						
7100208		Wrench for Po	eidential Housing	ne	1			
l		1						
 								
	Dual Mean			iltor Housings	- 1			
	Dual Wrenc	ii ioi iviembrane a	and Residential F	TILET HOUSINGS	1			
5								
1		Mounting Screws for standard Housings						
7300393					1			
1		Mounting Screws ounting Screws fo			1			
7300393								
7300393 7300395		ounting Screws fo	or Full Flow Hous					
7300393		ounting Screws fo O-Ring for sta			1			
	7100589 7100270 7100271 7100272 7100273 7100274 7100275 7100284 7100285 Housings 7100277 7100277 7100278 7100279 7100280 7100281 Housings 7100282 7100283 Pusings 7100286 7100287 7100288 7100287 7100288 7100289 7100290 Pusings 7100291 7100292 7100293 7100294 7100295 Sings (200° 7100297 ets - include 7300605 7100463	7100589 5" 7100270 10" 7100271 10" 7100272 10" 7100273 10" 7100274 10" 7100275 10" 7100284 10" 7100285 20" Housings 7100276 10" 7100277 10" 7100277 10" 7100278 10" 7100281 10" 7100280 10" 7100281 10" 7100281 10" 7100282 20" 7100283 20" 7100283 20" 7100283 10" 7100285 10" 7100287 10" 7100287 10" 7100288 10" 7100289 10" 7100290 10" busings 7100290 10" busings 7100291 20" 7100292 20" 7100293 20" 7100295 20" Sings (200°F / 93°C) 7100296 10" 7100297 20" ets - includes hous 7300605 7100464 10" 7100465 7100466 7100467 7100468	7100270	7100589 5" ½" White	T100270			

