

WAYNE®

| UTILITY | sump | sewage | well | lawn | pool | specialty |

UTILITY PUMPS

transfer

PORTABLE CAST IRON TRANSFER PUMP

- Pumps Up To 1450 GPH @ 0'
- Cast Iron Transfer Utility Pump
- Boosts Line Pressure Up To 40 PSI
- 3/4" Brass Hose Adapters Connect To Standard Garden Hose
- Portable Transfer Pump You Can Take Anywhere and Plug In
- Easy-Prime Priming Outlet
- Applications include drainage, dewatering flooded basements, emptying stock tanks, draining water heaters, and charging polyglycol radiant heating lines
- Easy-Carry Cast Iron Handle For Portability
- Reinforced Thermoplastic Suction Strainer Included
- PC4K Kit Includes: 1/2 HP Cast Iron Transfer Pump, Reinforced Thermoplastic Storage Case, Suction Strainer, and 3/4" Brass Hose Adapters



PERFORMANCE

Discharge Pressure Per Square Inch	Suction Lift Gallons Per Hour - in feet			
	0'	5'	10'	15'
PSI				
5	1450	1420	1350	1270
10	1370	1300	1230	1160
15	1250	1190	1120	1040
20	1140	1070	1000	930
25	1020	950	880	810
30	890	820	750	570
35	750	680	620	550
40	610	540	480	410

WAYNE®

Customer Service: 1-800-237-0987
Web Site: www.waynepumps.com