PFPCVS600 Series PVC Spring Check Valves



Product Features

- Constructed from durable Type 1 PVC
- Spring loaded flapper for positive closing
- 1/2 lb. spring on flapper reduces water hammer
- Full flow design reduces flow loss
- True union design for easy installation & servicing
- · Socket end connections
- Can be installed vertically or horizontally
- Pressure rating: 125 PSI at 75° F (24° C)
- Conforms to ASTM D2466
- · Not for use with compressed air, gases or potable water
- Maximum fluid temperature 140° F (60° C)



PFPCVS600J 1-1/2 PVC SW UNION CHK VLV 1/2LB SPRG
PFPCVS600K 2 PVC SW UNION CHK VLV 1/2LB SPRG

Dimensional Data


Model	PFPCVS600J		PFPCVS600K	
Dimensions	In	mm	In	mm
IPS Pipe Size	1-1/2"	38.1	2"	50.8
Weight	1.2 lbs.	.5 kg	2.0 lbs.	.9 kg
А	3.35	85.0	3.94	100.0
В	3.54	90.0	4.36	110.7
С	8.94	227.1	10.63	270.0
D	3.63	92.2	4.36	110.7

Product Specifications

NO.	PART	MATERIAL	QTY
1	Union Socket	PVC	2
2	0-Ring	BUNA-N	2
3	Union Nut	PVC	2
4	Upper Body	PVC	1
5	Flapper Spring	304 Stainless Steel	1
6	Flapper Disc	PVC	1
7	Flapper Seat	BUNA-N	1
8	Flapper Hinge	PVC	1
9	Lower Body	PVC	1



PFPCVS600K



Warranty and Codes

This PROFLO product carries a 1-year limited warranty.