SharkBite® 2XL

For Copper, CPVC, or PEX Pipe

DESCRIPTION

LARGE BORE SharkBite Commercial is an extensive range of SharkBite Fitting and full flow Ball Valves in sizes 11/4", 11/2", & 2" Copper Tube Size (CTS) suitable for use with Copper, PEX,(SharkBite Tube Liner must be fitted to the PEX Pipe) and CPVC pipe. Use in commercial and residential applications for potable water, hydronic heating, chilled water and general water distribution for irrigation.

FEATURES AND BENEFITS

Quick Connect:

No tools, soldering, clamps, unions or glue required. Cut pipe square, de-burr to remove rough edges/debris, mark the pipe for correct depth and push to get a pressure ready connection every time.

Ouick Disconnect:

Disconnect in seconds by sliding the De-Mount Tool down the pipe to engage the demount lugs and rotate clockwise to lock the open position leaving both hands free, you can now remove the pipe.

SAFE-Recessed Release Collar:

Commercial SharkBite require a special Demount Tool and cannot be accidentally disconnected/released.

Extensive Range Including Slip Feature on Couplings and Tee's:

When repairing or tapping into existing pipe with "Push-Fittings" you must be able to either move the fitting or the pipe to ensure the pipe is engaged fully into the fitting. With rigid pipe like copper the only way with "Push-Fittings" is to have a SLIP feature to allow easy installation when tapping into existing pipe.

Easy Installation:

Unlike the tool intensive connection methods there is NO need to send multiple fitters to a job, SharkBite Commercial has been designed to be installed or removed by one person. All fittings are lubricated for easy connection and by fitting the De-Mount Tool before engaging the pipe the force required can be reduced further.

With the De-Mount Tool locked on you also have hands free disconnection.

WET OR DRY: No waiting for copper tube to dry before soldering or glue to cure, SharkBite makes an instant connection in seconds.

No Tools:

Unlike alterative tool intensive connections systems, SharkBite has no special tooling required for installation.

No Time:

Fastest connection - CUT-PUSH-DONE.

Easy access to small or confined places.

No Flame - Does not require fire permit or fire marshal.

No Waste:

Should you make an error or simply want to change your installation, no problem for SharkBite. Simply remove and re-use. (Fittings used for repeated testing must not be used in any permanent application).

Fittings Cannot be Disassembled:

SharkBite Commercial Fitting are factory assembled and components cannot be removed.

Long Pipe Engagement:

Provides pipe support against lateral pipe forces.

Lead Free (LF) Dezincification Resistance (DZR) Brass:

Exceeds current no lead legislation - AB1953 or NSF372. Suitable for underground installation subject to local code authorites/inspectors. Dezincification properties (DZR) exceed ISO6509 and NSF-14.

Environmentally Friendly:

Remove and re-use fittings, no need to be scrapped.

No heat is required for installation.


SPECIFICATION

SharkBite Commercial fittings are designed to operate over a wide range:

Temperatures from 20°F to 200°F.

Maximum working pressure of 200psi.

Design for use on ASTM B88 hard drawn & annealed copper type K, L, or M, ASTM F876 & F877 PEX and ASTM D2846/D2846M CPVC water pipe.







SharkBite® 2XL

For Copper, CPVC, or PEX Pipe

SPECIFICATION DATA-FITTINGS

Body......DZR Brass-Lead Free Alloy. O Ring......Chloramine Resistant EDPM O-Ring.

Tube Liner. Copper.

Grab Ring......316 Stainless Steel. SharkBite Cartridge Assembly...... Acetyl Copolymer.

SPECIFICATION DATA-VALVES

Body......DZR Brass-Lead Free Alloy. Cap......DZR Brass-Lead Free Alloy. Spindle......DZR Brass-Lead Free.

Seat.....PETF. Handle.....Mild Steel.

CONNECTIONS

Tube Connections......CTS.


Threaded Connections Male or Female NPT.

Street Connections......CTS.


CERTIFICATIONS

IAPMO IGC 157: Ball Valves-This standard covers material, testing, dimensional and performance requirements. ASSE1061: Fittings-Performance requirements for removable & non-removable push-fit fittings.

TYPICAL INSTALLATION




TYPICAL REMOVAL






SharkBite® 2XL


For Copper, CPVC, or PEX Pipe



P/N C 3.26″ Weight SB0135 0.84 4.37 SB0141 11/2" 11/2" 1.15 SB0154 4.80" 1.56 SB013528 0.69 11/2" 11/4" 4.37" 1.02 SB015441 4.80" 1.42




45° Elbow					
P/N	Α	В	C	Weight	
SB0535	11/4"	11/4"	5.15"	0.97	
SB0541	11/2"	11/2"	5.77"	1.35	
SB0554	2″	2"	6.50"	1.91	




Female Connector

. ca.e coeeto.				
P/N	Α	В	C	Weight
SB113532F	11/4"	1¼"FNPT	2.98"	0.72
SB114140F	11/2"	1½" FNPT	3.21"	0.92
SB115450F	2"	2" FNPT	3.42"	1.23




Male Connector

P/N	Α	В	С	Weight
SB113532M	11/4"	1¼"MNPT	3.03"	0.71
SB114140M	1½"	11/2" MNPT	3.20"	0.89
SB115450M	2"	2" MNPT	3.43"	1.20




P/N	Α	В	С	Weight
SB0235	11/4"	11/4"	2.80"	1.07
SB0241	1½"	1½"	3.16"	1.52
SB0254	2"	2"	3.60"	2.18



Street 45° Elbow

P/N	Α	В	C	D	Weight
SB0735	11/4"	11/4"	4.24"	5.45"	0.97
SB0741	11/2"	11/2"	4.70"	6.05"	1.35
SB0754	2"	2"	5.30"	6.74"	1.91



Slip Coupling

P/N	Α	В	С	Weight
SB0635	11/4"	11/4"	6.69"	1.20
SB0641	11/2"	1½"	7.40"	1.71
SB0654	2"	2"	7.98"	2.33




Demount Clip

P/N	Size	Weight
SBDC35	11/4"	0.07
SBDC41	11/2"	0.08
SBDC54	2"	0.09



Pex Stiffener

P/N	Size	Α	В	Weight
SBLT35	11/4"	1.65"	1.34"	0.08
SBLT41	11/2"	1.89"	1.59"	0.10
SBLT54	2"	2.09"	2.09"	0.15




ь	e	e	

P/N	Α	В	С	D	Weight
SB0335	11/4"	11/4"	11/4"	6.50"	1.61
SB0341	1½"	1½"	11/2"	6.70"	2.26
SB0354	2"	2"	2"	7.99"	3.07
SB03353516	11/4"	1/2"	11/4"	6.70"	1.25
SB03353522	11/4"	3/4"	11/4"	6.70"	1.28
SB03353528	11/4"	1″	11/4"	6.70"	1.42
SB03414122	11/2"	3/4"	11/2"	7.39"	1.78
SB03414128	11/2"	1"	11/2"	7.39"	1.92
SB03414135	11/2"	11/4"	1½"	7.39"	2.08
SB03545428	2"	1"	2"	7.99"	2.55
SB03545435	2"	11/4"	2"	7.99"	2.72
SB03545441	2"	11/2"	2"	7.99"	2.86



Ena Stop						
P/N	Size	Α	Weight			
SB0435	11/4"	2.35"	0.57			
SB0441	11/2"	2.62"	0.82			
SB0554	2"	2.89"	1.25			



Ball Valve

Dan varve					
P/N	Size	Α	В	Weight	
BBV435	11/4"	6.08"	5.10"	2.06	
BBV441	11/2"	6.79"	6.10"	2.99	
BBV454	2"	7.58"	6.16"	4.45	

^{*} All weights are in pounds