

|                                       |                                    |
|---------------------------------------|------------------------------------|
| Item #:<br><b>P4305-084</b>           | UPC Code:<br>844349010722          |
| Product Family Name:                  | Finish:<br><b>Brushed Nickel</b>   |
| Category:<br><b>Low Voltage Track</b> | Category Type:<br><b>LightRail</b> |
| Certification<br><b>N/A</b>           |                                    |
| Patents                               |                                    |
| Notes:                                |                                    |



Shade Detail

Image File Name:  
P4305-084.jpg



## MEASUREMENTS

|                                 |                            |                                     |                            |
|---------------------------------|----------------------------|-------------------------------------|----------------------------|
| Width:<br><b>5</b>              | Length:                    | Height:<br><b>10</b>                | Extension:                 |
| Height Adjustable:<br><b>No</b> | Min Overall Height:        | Max Overall Height:                 | Slope:<br><b>No</b>        |
| Wire Length:<br><b>7</b>        | Chain Length:              | Safety Cable Included:<br><b>No</b> | Net Weight:<br><b>6.79</b> |
| Canopy Width:<br><b>5</b>       | Canopy Height:<br><b>5</b> | Canopy Length:                      |                            |
| Backplate Width:                | Backplate Height:          | Center to Top:                      | Center to Bottom:          |

## LAMPING

|                               |                                 |                                   |                                 |                                 |
|-------------------------------|---------------------------------|-----------------------------------|---------------------------------|---------------------------------|
| No. of Bulbs:<br><b>5</b>     | Light Type:<br><b>1w Led</b>    |                                   |                                 |                                 |
| Max Bulb Wattage:<br><b>3</b> | Socket:<br><b>3w Led Module</b> |                                   |                                 |                                 |
| Dimmable:<br><b>Yes</b>       | Ballast:                        | Rated Life Hours:<br><b>30000</b> | Photocell Included:<br><b>N</b> | Lamps Included:<br><b>Yes</b>   |
| LED Included:<br><b>Yes</b>   | Color Temp.:<br><b>3000</b>     | CRI:<br><b>78</b>                 | Initial Lumens:                 | Delivered Lumens:<br><b>205</b> |



## SHIPPING

|                             |                                    |  |                          |
|-----------------------------|------------------------------------|--|--------------------------|
| Carton Width:<br><b>6</b>   | Carton Height:<br><b>10</b>        | Carton Length:<br><b>41.5</b>          |                          |
| Carton Weight:<br><b>11</b> | Carton Cubit Feet:<br><b>1.441</b> | Small Package Shippable:<br><b>Yes</b> |                          |
| Master Pack Width:          | Master Pack Height:                | Master Pack Length:                    |                          |
| Master Pack Weight:         | Master Cubic Feet:                 | Multi-Pack:                            | Master Pack:<br><b>1</b> |

## SHADE / GLASS

|              |                             |         |
|--------------|-----------------------------|---------|
| Description: | Material:<br><b>Acrylic</b> |         |
| Part No.:    | Quantity:                   |         |
| Width:       | Height:                     | Length: |

**LED**

LED

Yes



ETL Intertek

Yes