

Item #: **P565-077-L**  
 Product Family Name:  
 Category: **Wall Sconce**  
 Certification  
 Patents  
 Notes:

UPC Code: **844349014164**  
 Finish: **Chrome**  
 Category Type: **Sconce**



Mounted Horizontally or Vertically

Image File Name:  
 P565-077-L--  
 1377187930.jpg



## MEASUREMENTS

Width:	Length:	Height:	Extension:
<b>4.5</b>		<b>16.75</b>	<b>3.75</b>
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
<b>No</b>			<b>No</b>
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
<b>7</b>		<b>No</b>	<b>6.83</b>
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

## LAMPING

No. of Bulbs:	Light Type:			
<b>1</b>	<b>12w Led</b>			
Max Bulb Wattage:	Socket:			
<b>12</b>	<b>12w Led Module</b>			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
<b>Yes</b>		<b>30000</b>	<b>N</b>	<b>Yes</b>
LED Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
<b>Yes</b>	<b>3000</b>	<b>81</b>	<b>1026.74</b>	<b>693.74</b>



## SHIPPING

Carton Width:	Carton Height:	Carton Length:
<b>6.25</b>	<b>7.88</b>	<b>19.63</b>
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
<b>4.63</b>	<b>0.559</b>	<b>Yes</b>
Master Pack Width:	Master Pack Height:	Master Pack Length:
<b>8.66</b>	<b>13.385</b>	<b>20.47</b>
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
<b>10.23</b>		<b>2</b>

## SHADE / GLASS

Description:	Material:
	<b>Glass</b>
Part No.:	Quantity:
	<b>1</b>
Width:	Height:
<b>4.13</b>	<b>16</b>
	Length:
	<b>2.63</b>

**LED**

LED

**Yes**



Damp Location  
**Yes**