

MINKA-LAVERY®


Item #: **1005-44-PL**
 Product Family Name:
 Category: **Flush Mount**
 Certification: **E185183 ABI**
 Patents
 Notes:

UPC Code: **747396053059**
 Finish: **WHITE**
 Category Type: **Fluorescent**



Image File Name:

1005-44-PL--
1377113716.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
12	27.5	5	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	5.05
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs:	Light Type:			
2	T8-17w, G13 Fluorescent Tube			
Max Bulb Wattage:	Socket:			
17	G13 (T8)			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
No				No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHIPPING

Carton Width:	Carton Height:	Carton Length:
14	5.875	29.625
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
6.6	1.41	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
14.5	12.75	30.25
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
14.41		1
		Master Pack:
		2

SHADE / GLASS

Description:	Material:
	Acrylic
Part No.:	Quantity:
G1005	1
Width:	Height:
11.88	4.75
	Length:
	27.5



Damp Location
Yes



Title 17
Yes



Title 24
Yes



UL Listed
Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties

Rev 12.31.2015