

MINKA-LAVERY®

Item #:	UPC Code:
1013-44-PL	747396066660
Product Family Name:	Finish:
	WHITE
Category:	Category Type:
Flush Mount	Fluorescent
Certification	
E185183 ABI	
Patents	
Notes:	



Image File Name:
1013-44-PL--
1377113716.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
6.25	26.75	4.5	4.5
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	3.7
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs:	Light Type:			
2	T8-17w,G13,Fluorescent Tube			
Max Bulb Wattage:	Socket:			
17	G13,T8			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
No				No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
8.5	10.63	29.25	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
4.994	1.529	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
		1	1

SHADE / GLASS

Description:	Material:	
	Acrylic	
Part No.:	Quantity:	
G1013	1	
Width:	Height:	Length:
6.25	4.5	26.75



ENERGY
STAR
Yes



Damp
Location
Yes



Title 17
Yes



Title 24
Yes



UL Listed
Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties

Rev 12.31.2015