

MINKA-LAVERY®

Item #: **6813-66** UPC Code: **747396057163**
 Product Family Name: **Agilis™** Finish: **BLACK**
 Category: **Bath** Category Type: **Bath**
 Certification: **E127416**
 Patents:
 Notes:



Image File Name:
 6813-66--
 1377127940.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
32			8.75
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No	8.25		No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	9.94
Canopy Width:	Canopy Height:	Canopy Length:	
6.75	6		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:
		4.5	4

LAMPING

No. of Bulbs:	Light Type:			
3	A19 Med			
Max Bulb Wattage:	Socket:			
100	E27 Med			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes				No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHIPPING

Description:	Material:
	Glass
Part No.:	Quantity:
G6810	3
Width:	Height:
	Length:

Carton Width:	Carton Height:	Carton Length:
10.5	10.5	37
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
12.76	2.361	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		1
		Master Pack:
		1

SHADE / GLASS



Damp Location
 Yes



Title 17
 Yes



UL Listed
 Yes