

MINKA-LAVERY®

Item #: 829-86	UPC Code: 747396023717
Product Family Name:	Finish: TEXTURED WHITE
Category: Flush Mount	Category Type: Flush Mount
Certification E183922	
Patents	
Notes:	



Image File Name:

829-86--
1377129264.jpg



MEASUREMENTS

Width: 13.5	Length:	Height: 6	Extension:
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 4.01
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

LAMPING

No. of Bulbs: 2	Light Type: A19 Med			
Max Bulb Wattage: 60	Socket: E27 Med			
Dimmable: No	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:

SHADE / GLASS

Description:	Material: Glass
Part No.: G829	Quantity: 1
Width: 9.88	Height: 3.75
	Length:



SHIPPING

Carton Width: 13.75	Carton Height: 6.75	Carton Length: 13.75
Carton Weight: 5.324	Carton Cubic Feet: 0.739	Small Package Shippable: Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1
		Master Pack: 1



Damp Location
Yes



Title 17
Yes



UL Listed
Yes

For additional information, please contact Customer Care: 1-800-221-7977

Product depicted on this spec sheet is protected by United States Federal and/or State laws including US Patent, Trademark and/or Copyright and unfair competition laws. Unauthorized reproduction or use carries severe legal penalties

Rev 12.31.2015