

Item #: 8611-A61	UPC Code: 747396080031
Product Family Name: Taylor Court™	Finish: Vintage Rust™
Category: Wall Mount	Category Type: Wall Bracket
Certification 3057374	
Patents	
Notes:	



Image File Name:
8611-A61--
1377129548.jpg



MEASUREMENTS

Width: 6.5	Length: 6.5	Height: 12.75	Extension: 8.13
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 2.23
Canopy Width: 5.25	Canopy Height: 7	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top: 6.25	Center to Bottom: 6.5

SHADE / GLASS

Description:	Material: Glass
Part No.:	Quantity: 1
Width: 2.5	Height: 4.63
	Length:

LAMPING

No. of Bulbs: 1	Light Type: A-19,Med			
Max Bulb Wattage: 60	Socket: E26,Med			
Dimmable: Yes	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included: No
Lamp Included: No	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:



SHIPPING

Carton Width: 8.25	Carton Height: 15	Carton Length: 10	
Carton Weight: 3.454	Carton Cubic Feet: 0.716	Small Package Shippable: Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack: 1	Master Pack: 1



Wet Location

Yes



ETL Intertek

Yes