

## Features

- Unique articulated-joint design directs water to any angle and folds out of the way when not in use.
- Single 1-5/16" (33 mm) diameter remote joystick lever handle is simple to use and makes adjusting water temperature easy.
- Ceramic disc valves exceed industry longevity standards, ensuring durable performance for life.
- Integral sprayhead provides laminar flow or aerated spray at the touch of a button
- Variable spout reach from less than 2" (51 mm) to over 13" (330 mm)
- 1.8 gallons (6.8 L) per minute maximum flow rate at 60 psi (4.1 bar)
- Meets CalGreen requirements for kitchen faucets.

## Material

- Premium metal and carbon fiber construction.
- KOHLER finishes resist corrosion and tarnishing.

## Installation

- 2-Hole Deck-mount
- Flexible supply lines and installation ring simplify installation.

## Optional Accessories

1191733 Deep Rough-in Kit



**ADA**

## Codes/Standards

ASME A112.18.1/CSA B125.1

NSF 61

NSF 372

DOE - Energy Policy Act 1992

ADA

ICC/ANSI A117.1



All applicable US Federal and State material regulations


## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

## Available Color/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	VS	Vibrant® Stainless



## Technical Information

All product dimensions are nominal.

Spout reach: 6" (152 mm)

### Faucet:

Flow rate: 1.8 gal/min (6.8 l/min)

Pressure: 60 psi (4.1 bar)

## Notes

Install this product according to the installation guide.

ADA compliant when installed to the specific requirements of these regulations.