# Perlator® Honeycomb® Faucet Aerator - 2.2 gpm max Flow Restricted Regular Size



flow, stop and go®

### **Features and Benefits**

- Watercolours® design: Color coding to identify flow rate and stream pattern.
- Patented construction provides a splash-free stream, well aerated and soft to the touch.
- Integrated anti-liming Honeycomb® replaces conventional wire mesh screens prone to lime build up.
- Anti-clogging dome screen filters sediment and particles.
- Also compatible with regular and vandal proof M22 and M24 metric housings.
- Available housing finishes: chrome, polished brass, brushed nickel and oil rubbed bronze.
- Laser marked housings with statutory mark.

### Certifications

ANSI/NSF®-61-372 (10926 pending) ASME A112.18.1M and CSA B125

Thread & Part Number					
Part #	Designation	Thread Size			
10 935	Insert only				
10 900	Regular male	15/16"-27			
10 910	Regular female	55/64"-27			
10 920	Regular dual thread	15/16"-27 x 55/64"-27			
10 904	Vandal proof regular male	15/16"-27			
10 914	Vandal proof regular female	55/64"-27			
10 926	Vandal proof regular dual thread	15/16"-27 x 55/64"-27			


Other product combinations available.

## Packaging:


Inserts 1pc (bag), 6pcs (tube), 50pcs (tray)
Reg. male/female/dual thread 1pc (bag), 6pcs (tube), 50pcs (tray)
Reg. vandal proof male/female/dual thread 1pc (bag), 6pcs (tube), 40pcs (tray)

Color Code					
Dome	Ring	Basket			
Red	Red	Dark Grav			

# Flow Rate Curve







Dimensions						
No	mm	In				
А	20.88	.822				
В	12.00	.472				
С	19.97	.786				
D	≈ 13	≈ 1/2				



Technical Data						
Materials:	Materials: Body		Acetal			
	Washer	EPD	М			
Continuous		Short-term (5 minutes max.)				
max. 50 120		max. 160				
°C •F	90 psi 6 bar max.		8.5 bar max.			