Perlator® Honeycomb® Faucet Aerator - 1.5 gpm max Flow Restricted Regular Size



flow, stop and go®

Features and Benefits

- Watercolours® design: Color coding to identify flow rate and stream pattern.
- Patented construction provides a splash-free stream, well aerated and soft to the touch.
- Integrated anti-liming Honeycomb® replaces conventional wire mesh screens prone to lime build up.
- Anti-clogging dome screen filters sediment and particles.
- Also compatible with regular and vandal proof M22 and M24 metric housings.
- Available housing finishes: chrome, polished brass, brushed nickel and oil rubbed bronze.
- Laser marked housings with statutory marks.

Certifications

ANSI/NSF®-61-372 ASME A112.18.1M and CSA B125 Meets *CAL* **Green** requirements

WaterSense



Thread & Part Number					
Part #	Designation	Thread Size			
10 635	Insert only				
10 600	Regular male	15/16"-27			
10 610	Regular female	55/64"-27			
10 620	Regular dual thread	15/16"-27 x 55/64"-27			
10 604	Vandal proof regular male	15/16"-27			
10 614	Vandal proof regular female	55/64"-27			
10 626	Vandal proof regular dual thread	15/16"-27 x 55/64"-27			


Other product combinations available.

Packaging:


Inserts 1pc (bag), 6pcs (tube), 50pcs (bag)
Reg. male/female/dual thread 1pc (bag), 6pcs (tube), 50pcs (tray)
Reg. vandal proof male/female/dual thread 1pc (bag), 6pcs (tube), 40pcs (tray)

Color Code				
Dome	Ring	Basket		
Green	Green	Dark Gray		

Flow Rate Curve







Dimensions						
No	mm	In				
Α	20.88	.822				
В	12.00	.472				
С	19.97	.786				
D	≈ 13	≈ 1/2				



Technical I	Technical Data						
Materials:	Body	Acetal					
	Washer	EPDM					
Continuous		Short-term (5 minutes max.)					
max. 120		max. 160					
°C 🔵 °F	90 psi 6 bar max.	°C 🔵 °F	125 psi 8.5 bar max.				