

PCA® Perlator® Honeycomb® Faucet Aerator - 1.2 gpm max Pressure Compensating Regular Size




flow, stop and go®

Features and Benefits

- ▶ Watercolours® design: Color coding to identify flow rate and stream pattern.
- ▶ Patented construction provides a splash-free stream, well aerated and soft to the touch.
- ▶ Pressure compensating for constant flow from 20 to 80 psi.
- ▶ Integrated anti-liming Honeycomb® replaces conventional wire mesh screens prone to lime build up.
- ▶ Anti-clogging dome screen filters sediment and particles.
- ▶ Also compatible with regular and vandal proof M22 and M24 metric housing.
- ▶ Available housing finishes: chrome, polished brass, brushed nickel and oil rubbed bronze.
- ▶ Laser marked housings with statutory marking.

Certifications

ANSI/NSF®-61-372
ASME A112.18.1M and CSA B125
Meets **CALGreen** requirements
WaterSense
Complies with CEC Amendment to CCR Title 20, section 1605.3



Thread & Part Number

Part #	Designation	Thread Size
14 535	Insert only	
14 500	Regular male	15/16"-27
14 510	Regular female	55/64"-27
14 520	Regular dual thread	15/16"-27 x 55/64"-27
14 504	Vandal proof regular male	15/16"-27
14 514	Vandal proof regular female	55/64"-27
14 526	Vandal proof regular dual thread	15/16"-27 x 55/64"-27

Other product combinations available.


Packaging:

Inserts *1pc (bag), 6pcs (tube), 50pcs (bag)*
Reg. male/female/dual thread *1pc (bag), 6pcs (tube), 50pcs (tray)*
Reg. vandal proof male/female/dual thread *1pc (bag), 6pcs (tube), 40pcs (tray)*

Color Code

Dome	Flow Regulator	Basket
Clear	Pink	Dark Gray

Flow Rate Curve



Dimensions

No	mm	In
A	20.88	.822
B	12.00	.472
C	19.97	.786
D	≈ 13	≈ 1/2

Housings



Technical Data

Materials: Body Acetal
O-ring EPDM
Washer EPDM

