

COLONY® 25 x 22 SINGLE BOWL STAINLESS STEEL KITCHEN SINK

O GAUGE STAINLESS STEE

COLONY® 25 x 22 SINGLE BOWL STAINLESS STEEL KITCHEN SINK

☐ 20SB.8252283S.075

- Colony Single Bowl Sink
- 3 hole
- 8" deep bowl
- 20 Gauge Stainless Steel
- Top Mount Installation
- Bottom Sound Deadening Pads with undercoating
- · Waste fitting included
- Cutout template, installation instructions and top mount hardward included
- 27" (686mm) cabinet required
- Limited Lifetime Warranty

☐ 20SB.8252284S.075

- Colony Single Bowl Sink
- 4 hole
- 8" deep bowl
- 20 Gauge Stainless Steel
- Top Mount Installation
- Bottom Sound Deadening Pads with undercoating
- Waste fitting included
- Cutout template, installation instructions and top mount hardward included
- 27" (686mm) cabinet required
- Limited Lifetime Warranty

Nominal Dimensions:

25" x 22" x 8" (635 x 559 x 203mm)

Each Bowl Size:

21-1/4" (540mm) wide 15-1/8" (384mm) front to back 8" (203mm) deep

Compliance Certifications - Meets or Exceeds the Following Specifications:

• SINK:

ASME A112.19.3

To Be Specified:

☐ Color: Stainless Steel .075




SEE REVERSE FOR ROUGHING-IN
DIMENSIONS AND PRODUCT SPECIFICATIONS



COLONY® 25 x 22 SINGLE BOWL STAINLESS STEEL KITCHEN SINK

20 GAUGE STAINLESS STEEL



NOTES:

** DIMENSIONS SHOWN FOR LOCATION OF SUPPLIED AND "P" TRAP ARE SUGGESTED. FITTINGS NOT INCLUDED WITH FIXTURE AND MUST BE ORDERED SEPARATELY. SEALING COMPOUND SUPPLIED BY OTHERS.

IMPORTANT: Dimensions of fixtures are nominal and may vary within the range of tolerances established by ANSI Standard A112.19.3. These measurements are subject to change or cancellation. No responsibility is assumed for use of superseded or voided pages.