


'Apollo' Valves

SUBMITTAL SHEET

LEAD FREE

70LF-100/200 HC Series

Bronze **Ball Valve** with 3/4" Hose Connection and Protective Cap & Chain



Job Name:	
Job Location:	
Engineer:	
Contractor:	
Tag:	
PO Number:	
Representative:	
Wholesale Distributor:	



DESCRIPTION

The Apollo® 70LF-HC models are ideally suited for direct connection to hoses. Valves feature a heavy duty machined hose thread cover with chain to prevent loss. Standard lever and nut are stainless steel.

FEATURES

- NPT or Solder End x 3/4" NPSH
- Full Pressure Rated Heavy Brass Hose Cap
- Lead Free* Brass & Bronze Materials
- Distinctive white "Lead Free" handle grip and blue "Lead Free" hang tag
- Blow-Out-Proof Stem Design
- Adjustable Packing Gland
- Premium RPTFE Seats and Stem Packing
- Stainless steel lever and stem nut
- 100% Factory Tested
- Made in USA

PERFORMANCE RATING

- Maximum Pressure: 600 psi CWP
- Maximum Temperature: 210°F
- Vacuum Service to 29 in. Hg

APPROVALS

- MSS SP-110; Ball Valves Threaded, Socket-Welding, Solder Joint, Grooved and Flared Ends
- ANSI 3rd Party Approval to 0.25% Lead Max.
- ANSI/NSF 61 Section 8
- ANSI/NSF 372 3rd party certified

OPTIONS & SIZES


- (-04) 2 1/4" CS Stem Extension 1/2" - 1"
- (-07) Steel Tee Handle 1/2" - 1"
- (-11) Therma-Seal™ Insulating Tee Handle 1/2" - 1"
- (-15) Wheel Handle, Steel 1/2" - 1"
- (-27) SS Latch-Lock Lever & Nut 1/2" - 1"
- (-94) 2-1/4" Extension w/ Balancing Stop 1/2" - 1"
- 70LF-140 & 70LF-240 series w/ SS Ball & Stem 1/2" - 1"

STANDARD MATERIALS LIST

Part Name	Material
Lever and Grip	Stainless Steel w/ Vinyl
Stem Packing	MPTFE
Stem Bearing	RPTFE
Ball	C27451 Lead Free* Brass, Cr Plated
Seat (2)	RPTFE
Retainer	C27451 Lead Free* Brass
Gland Nut	C27451 Lead Free* Brass
Stem	C27451 Lead Free* Brass
Lever Nut	Stainless Steel
Body	C89836 Lead Free* Bronze
Hose Cap	ASTM B16 Brass

DIMENSIONS

Part Number	Size (in.)	Dimensions (in.)								Wt. (lbs.)
		A	B	C	D	E	F	G	H	
NPT X 3/4" HOSE THREAD										
70LF-103-HC	1/2"	0.50	1.09	2.75	2.99	1.94	4.18	-	-	0.63
70LF-104-HC	3/4"	0.68	1.50	3.41	3.66	2.32	5.31	-	-	1.30
70LF-105-HC	1"	0.87	1.92	3.92	4.16	2.43	5.28	-	-	1.72
SOLDER X 3/4" HOSE THREAD										
70LF-203-HC	1/2"	0.50	1.42	3.08	3.32	1.94	4.18	0.63	0.50	0.71
70LF-204-HC	3/4"	0.68	1.93	3.84	4.09	2.32	5.31	0.88	0.75	1.44



* LEAD FREE: The wetted surfaces of this product shall contain no more than 0.25% lead by weighted average. Complies with CA AB1953, VT Act 193, MD HB372, LA HB471 and Federal Public Law 111-380. ANSI 3rd party approved and listed.

Apollo Valves, Manufactured by **Conbraco Industries, Inc.**
701 Matthews Mint-Hill Road, Matthews, NC 28105 USA
www.apollovalves.com | (704) 841-6000

This specification is provided for reference only. Conbraco Industries Inc. reserves the right to change any portion of this specification without notice and without incurring obligation to make such changes to Conbraco products previously or subsequently sold. Please visit our website at www.apollovalves.com for the most current information.

