

Model YBXL

Domestic Bronze "Y" Type Strainer

Application

Designed for installation on potable water lines to protect against sediment and debris. Ideal for use where lead-free* fittings are required.

Standards Compliance

- Conformance to MIL-S-16293
- Certified to NSF/ANSI 372* by IAPMO R&T
 *(0.25% MAX. WEIGHTED AVERAGE LEAD CONTENT)

Materials

Main valve body Low Lead Cast Bronze ASTM B 584 Access covers Low Lead Bronze ASTM B 584 or

Low Lead Brass

Screens 20 Mesh Stainless Steel, 300 Series

Features

Sizes: 1/2", 3/4", 1", 1 1/4", 1 1/2", 2", 2 1/2", 3"

Pressure / Temperature:

MODEL YBXL 400 psi@ 180°F WOG

MODEL YBXLC 400 psi@ 150°F

End Connections Threaded ANSI B 1.20.1 (Closure plug available but not standard, sizes 1/2" - 2";

plug standard on 2 1/2" & 3")







Options (Suffixes can be combined)


P - with tapped access cover & pipe plug
C - with copper sweat connections (1/2" - 2")

40 - with 40 mesh strainer screen
60 - with 60 mesh strainer screen
80 - with 80 mesh strainer screen
100 - with 100 mesh strainer screen

Dimensions & Weights (do not include pkg.)

MODEL YBXL (NPT CONNECTION)										
SIZE		D	WEIGHT							
		A		В		С	I WEIGHT			
in.	mm	in.	mm	in.	mm	in.	lbs.	kg.		
1/2	15	3 1/8	79	2	51	3/8 NPT	1	0.5		
3/4	20	3 5/16	84	2 5/16	58	1/2 NPT	1	0.5		
1	25	4 1/2	114	3	76	3/4 NPT	2	1		
1 1/4	32	4 11/16	119	4 5/8	117	3/4 NPT	4	2		
1 12	40	5 3/16	130	5 1/8	130	3/4 NPT	5	2.5		
2	50	6 1/8	156	6 1/4	159	3/4 NPT	7	3		
2 1/2	65	8 1/4	210	7	178	1/2 NPT	14	6.5		
3	80	11 1/8	282	7 1/2	191	1/2 NPT	25	11.5		

MODEL YBXLC (COPPER SWEAT CONNECTION)										
SIZE		DIMENSIONS (approximate)						WEIGHT		
		A		В		С	VVEIGHT			
in	mm	in.	mm	in.	mm	in.	lbs.	kg		
1/2	15	3 5/16	84	2	51	3/8 NPT	1	0.5		
3/4	20	3 3/4	95	2 5/16	58	1/2 NPT	1	0.5		
1	25	5	127	3	76	3/4 NPT	2	1		
1 1/4	32	5 5/8	143	4 5/8	117	3/4 NPT	4	2		
1 1/2	40	6 7/16	164	5 1/8	130	3/4 NPT	5	2.5		
2	50	7 3/8	187	6 1/4	159	3/4 NPT	7	3		



Zurn Industries, LLC | Wilkins


1747 Commerce Way, Paso Robles, CA U.S.A. 93446 Ph. 855-663-9876, Fax 805-238-5766

In Canada | Zurn Industries Limited


3544 Nashua Drive, Mississauga, Ontario L4V 1L2 Ph. 905-405-8272, Fax 905-405-1292

Rev. A Date: 5/13 Document No. STR-YBXL Product No. Model YBXL

MODEL YBXL 1/2" thru 1 1/4" (STANDARD & METRIC)




MODEL YBXL 1 1/2" thru 3" (STANDARD & METRIC)



Typical Installation

Local codes shall govern installation requirements. Unless otherwise specified, the assembly shall be mounted in accordance with the latest edition of the Uniform Plumbing Code. If installed below grade, be certain adequate drainage is provided to prevent the device from being submerged. Horizontal installation with the strainer cap facing downward is the preferred installation orientation; however the strainer will provide protection in any orientation.



Specifications

The "Y" type strainer shall be domestically manufactured, and conform to MIL-S-16293, and be certified to NSF/ANSI 372. The main body shall be low lead bronze (ASTM B 584), the access cover shall be low lead yellow brass (ASTM B 16) or cast bronze (ASTM B 584), the strainer screen shall be 300 series stainless steel and available in 20, 40, 60, 80 or 100 mesh. Screens shall be accessible for cleaning without removing the device from the line. The "Y" type strainer shall be a ZURN WILKINS Model YBXL.