



Tea-for-Two®

6' Whirlpool Bath
K-865-HM

Features

- End drain.
- Integral lumbar support.
- 71-3/4" (1822 mm) x 36" (914 mm) x 20-7/8" (530 mm)

Material

- Cast iron with Safeguard® finish.

Hydrotherapy

- Six fully adjustable Flexjet™ hydrotherapy jets for water flow and direction.
- Built-in 1500 W heater.
- Multiple pump location options give you more choices for installation and access.
- Lighted keypad control.
- Remote control.

Installation

- Drop-in, under-mount, or alcove.

Required Accessories

K- 7169-AF 1-1/2" Contoured Pop-up Drain
K- 9696 Whirlpool 6-Jet Trim Kit

Recommended Accessories

K- 1179 Vinyl Tiling-in Bead
K- 582 Under-mount Installation Kit



Codes/Standards











ASME A112.19.1/CSA B45.2
ASME A112.19.7/CSA B45.10
UL 1795
CSA C22.2 No. 218.2
CARB P2


KOHLER® Lifetime Limited Warranty for Cast Iron Components

See website for detailed warranty information.


Available Color/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|--|------|---------------|
|  | 0 | White |
|  | 96 | Biscuit |
|  | 47 | Almond |
|  | NY | Dune |
|  | 95 | Ice™ Grey |
|  | G9 | Sandbar |
|  | 33 | Mexican Sand™ |
|  | K4 | Cashmere |
|  | 58 | Thunder™ Grey |
|  | 7 | Black Black™ |



No change in measurements if connected with drain illustrated. (K-7169-AF)



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Pump, Heater: 240 V, 20 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

| | |
|------------------------------|---|
| Installation: | Drop-in, Under-mount, 3-Wall Alcove |
| Drain location: | End |
| Basin area, bottom: | 49" x 22" (1245 mm x 559 mm) |
| Basin area, top: | 62" x 28" (1575 mm x 711 mm) |
| Weight: | 455 lbs (206.4 kg) |
| Minimum floor load: | 69 lbs/ft ² (336.9 kg/m ²) |
| Water depth: | 17" (432 mm) |
| Water capacity: | 89 gal (336.9 L) |
| Cutout: | Drop-in, 70-1/4" x 34-1/2" (1784 mm x 876 mm) |
| Template: | Under-mount, K-582, required, not included |
| Electrical component rating: | Pump: 240 V, 11 A Heater: 240 V, 6 A, 1500 W |

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Pump must be relocated to custom position at the time of installation. Provide adequate clearance.

Cast iron whirlpools are extremely heavy, making some drop-in installations difficult. Splitting the deck/surround is recommended if installing into a deck.