



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
7.00"	13.50"	8.50"
<u>BP Height</u>		
4.06"		
<u>Hanging Weight</u>		
4.58 lb		

Lamping:

Fluorescent GU24	1,800 Rated Lumens
2.00 13W GU24	2700 Color Temperature
26 total watt	10,000 Rated Life 81-82 CRI
Dimmable : No	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
6.50 lb	10.63"	12.13"	12.75"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209076532	Yes	

Finish:

Satin Nickel SN

Glass:

Frosted FT

Material:

Metal

Certification:

Damp Location
Y Location
CA Title 24

Additional:

GU24 (Included)
Lighting Direction: Both
Incandescent Watts: 164