



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
8.00"	19.00"	9.00"
<u>BP Height</u>	<u>BP Width</u>	
5.38"	5.38"	
<u>Hanging Weight</u>		
5.29 lb		

Lamping:

Fluorescent GU24	2,700 Rated Lumens
3.00 13W GU24	2700 Color Temperature
39 total watt	10,000 Rated Life 80+ CRI
Dimmable : No	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
6.55 lb	9.06"	11.22"	17.13"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209058668	Yes	

Finish:

Satin Nickel SN

Glass:

Ice IC

Material:

Steel

Certification:

Damp Location
Y Location
CA Title 24

Additional:

GU24 (Included)
Lighting Direction: Both
Incandescent Watts: 245