



*height from center of outlet to the top of the fixture

Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
15.00"	8.00"	8.00"
<u>BP Height</u>	<u>BP Width</u>	<u>HCO</u>
4.50"	4.50"	11.00"
<u>Hanging Weight</u>		
2.20 lb		

Lamping:

Fluorescent GU24	900 Rated Lumens
1.00 13W GU24	2700 Color Temperature
13 total watt	10,000 Rated Life 80+ CRI
Dimmable : No	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
3.34 lb	8.66"	12.60"	9.45"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
20.02 lb	19.69"	13.39"	27.17"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
6.0000	783209032316	Yes	

Finish:

Rust Patina RP

Glass:

Frosted FT

Material:

Die Cast Aluminum

Certification:

Wet Location
Y Location
CA Title 24

Additional:

GU24 (Included)
Incandescent Watts: 82