


CounterMax MX-X120 |
87832SN

Job Name: Job Type: Quantity: Comments:



Measurements:

<u>Height</u>	<u>Width</u>	<u>Length</u>
1.25"	5.00"	21.00"
<u>Hanging Weight</u>		
2.60 lb		

Lamping:

Xenon G8	675 Rated Lumens
3.00 20W G8	2900 Color Temperature
60 total watt	3,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
2.90 lb	6.50"	2.50"	25.30"
<u>Master Pack Weight</u>	<u>Master Pack Width</u>	<u>Master Pack Height</u>	<u>Master Pack Length</u>
18.10 lb	13.90"	9.40"	25.90"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
6.0000	783209107311	Yes	

Finish:

Satin Nickel SN

Material:

Aluminum

Certification:

Dry Location
N Location

Additional:

G8 (Included)