For Residential and Commercial Applications			
Job Name		Engineer / Architect	
Job Location		Wholesaler	
Submittal Date		Contractor	

SCR1B/ SCR09/ SCR19/ SCR39/ SCR49 Multi-Turn Angle Stop w/ Loose Key – Compression x Compression

Use: For use in potable water distribution systems. Not intended for recirculating water systems that produce continuous use temperatures above 115° F. For those applications, use our KT[™] series ball stops.

Design Features:

- Machined one-piece brass body provides strength, durability, and long-lasting performance
- Large loose key handle provides a secure grip for trouble-free on/off operation
- **Removable loose key handle** helps protect against accidental stop operation during rough-ins
- 🗹 No Lead
- For use with ASTM F876 PEX tubing, in ASTM F877 water distribution systems (parts containing PX and PXX only)
- For use in ASTM F877 water distribution systems as noted in Appendixes (parts containing PX and PXX only)

Operating Specifications:

Temperature:40°- 140° FPressure:125 PSI maximum

Standard

STOP MATERIAL SPECIFICATIONS		
Body	Brass, chrome plated	
Lock Shield Stem	Brass, chrome plated	
Bib & Packing Washer	Rubber	
Lock Shield	Brass, chrome plated	
Loose Key	Zinc die cast	
Compression Nut	Brass, chrome plated	
Compression Sleeve	Brass	
PEX Insert*	Stainless steel	

No Lead

STOP MATERIAL SPECIFICATIONS	
Body	No-Lead brass, chrome plated
Lock Shield Stem	No-Lead brass, chrome plated
Bib & Packing Washer	Rubber
Lock Shield	Brass, chrome plated
Loose Key	Zinc die cast
Compression Nut	Brass, chrome plated
Compression Sleeve	Brass
PEX Insert*	Stainless steel

MACHINED AND

*Where specified

Standard Part Listing:

	•
SCR1B C	3/8" nom compression x 3/8" OD compression, chrome plated
SCR09 C	1/2" nom compression x 1/4" OD compression with loose key, chrome plated
SCR09 R	1/2" nom compression x 1/4" OD compression with loose key, rough brass
SCR19 C	1/2" nom compression x 3/8" OD compression with loose key, chrome plated
SCR19 C1	1/2" nom compression x 3/8" OD compression with loose key, chrome plated, window box
SCR19 R	1/2" nom compression x 3/8" OD compression with loose key, rough brass

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft Mfg. This specification must be returned to BrassCraft Mfg. if requested.




400.33 SCR1B/09/19/39/49 Multi-Turn Angle Stop w/ Loose Key - Compr x Compr REV 08/13 © 2013 BrassCraft Mfg.

SCR1B/ SCR09/ SCR19/ SCR39/ SCR49 Multi-Turn Angle Stop w/ Loose Key – Compression x Compression

Standard Part Listing (con't):

SCR19PX C	1/2" Nom. compression x 3/8" OD compression with loose key, PEX stainless steel insert, chrome plated			
SCR39 C	1/2" Nom. compression x 1/2" OD compression with loose key, chrome plated			
SCR39 C1	$1/2^{\prime\prime}$ nom compression x $1/2^{\prime\prime}$ OD compression with loose key, chrome plated, window box			
SCR49 C	1/2" nom compression x 5/8" OD compression with loose key, chrome plated			
SSCR19 C	1/2" nom compression x 3/8" OD compression with screwdriver slot, chrome plated			
SSCR39 C	$1/2^{"}$ nom compression x $1/2^{"}$ OD compression with screwdriver slot, chrome plated			
SSCR49 C	1/2" nom compression x 5/8" OD compression with screwdriver slot, chrome plated			
No-Lead Part Listing:				
SCR1BX C	3/8" nom compression x 3/8" OD compression, chrome plated			
SCR09X C	1/2" nom compression x 1/4" OD compression with loose key, chrome plated			
SCR19X C	1/2" nom compression x 3/8" OD compression with loose key, chrome plated			
SCR19X C1	1/2" nom compression x 3/8" OD compression with loose key, chrome plated, window box			
SCR19X R	1/2" nom compression x 3/8" OD compression with loose key, rough brass			
SCR39X C	$1/2^{\prime\prime}$ nom compression x $1/2^{\prime\prime}$ OD compression with loose key, chrome plated			
SCR39X C1	$1/2^{\prime\prime}$ nom compression x $1/2^{\prime\prime}$ OD compression with loose key, chrome plated, window box			
SSCR19X C	1/2" nom compression x 3/8" OD compression with screwdriver slot, chrome plated			
SSCR49X C	1/2" nom compression x 5/8" OD compression with screwdriver slot, chrome plated			




Listings & Certifications:

- IAPMO listed to ASME A112.18.1 / CSA B125.1 (File # 0645)
- CSA listed to ASME A112.18.1 / CSA B125.1 (File # 204593)
- No-Lead product CSA listed to Low Lead Content Certification Program – Plumbing Products Class 6853-01



This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft Mfg. This specification must be returned to BrassCraft Mfg. if requested.

400.33 SCR1B/09/19/39/49 Multi-Turn Angle Stop w/ Loose Key - Compr x Compr REV 08/13



Brass

© 2013 BrassCraft Mfg.