



# Sunstruck® 5.5' BubbleMassage™ Bath K-1966-G



## Features

- Freestanding design creates a striking focal point in your bathing area.
- Integral lumbar support.
- 16" soaking depth.
- Wide ledge on one side is ideal for deck-mount faucet and/or handshower.
- Textured bottom surface.
- Center drain.
- 65-1/2" (1664 mm) x 35-1/2" (902 mm) x 24-1/2" (622 mm)

## Material

- Acrylic

## Hydrotherapy

- 118-122 BubbleMassage™ airjets.
- Variable-speed blower for adjusting hydromassage intensity.

## Installation

- Freestanding
- PureFlo drains are not recommended for a deck-mount faucet installation.

## Recommended Accessories

K-7265 Clearflo Bath Drain  
K-37383 30" Rough-in Cable Bath Drain  
K-37386 30" Rough-in Cable Bath Drain  
K-24916 Wireless Music Kit



## Codes/Standards

ASME A112.19.7/CSA B45.10  
CSA B45.5/IAPMO Z124  
UL 1795  
CSA C22.2 No. 218.2  
Greenguard UL 2818 - Gold  
CARB P2

## KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

## Available Color/Finishes


*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	
	96	

No change in measurements if connected with drain illustrated. (K-7213)

■ Faucet area.



\* Allow for appropriate clearance in subfloor for drain clearance.

Note: Horizontal PVC pipe and tee shown, not included.

### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Blower: 120 V, 15 A, 60 Hz

### Technical Information

All product dimensions are nominal.

Installation: Freestanding  
 Drain location: Center  
 Basin area, bottom: 45-3/4" x 24-7/8" (1162 mm x 632 mm)  
 Basin area, top: 54-7/8" x 29-3/16" (1394 mm x 741 mm)  
 Weight: 91 lbs (41.3 kg)  
 Minimum floor load: 40.4 lbs/ft² (197.3 kg/m²)  
 Water depth: 16" (406 mm)  
 Water capacity: 72.6 gal (274.8 L)  
 Template: Footprint, 1244408-7, not required, not included  
 Electrical component rating: Blower: 120 V, 10 A, 60 Hz, 300 W

### Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Provide one grounded electrical outlet within 24" (610 mm) of each component.

Remote blower motor installation is required. Relocation kit is included.

If installing a rim-mount faucet, make sure there is no interference with drain overflow before drilling any holes. Consult local and national codes for minimum air gap requirements if installing a spout on the faucet deck.