



# Underscore® 6' BubbleMassage™ Bath K-5718-G



## Features

- Center drain.
- Slotted overflow for deep soaking.
- Dual lumbar supports two-person bathing by offering comfort at both ends.
- 72" (1829 mm) x 42" (1067 mm) x 22" (559 mm)

## Material

- Acrylic

## Hydrotherapy

- 118-122 BubbleMassage™ airjets.
- Variable-speed blower for adjusting hydromassage intensity.
- Zones of Control feature allows you to target massage to back, midsection, or feet.
- Automatic purge cycles remove residual water from air channels after use.

## Installation

- Drop-in or undermount.

## Required Accessories

K-7271 Brass Slotted Overflow Bath Drain

or

K-7272 PVC Slotted Overflow Bath Drain

## Recommended Accessories

K-24916 Wireless Music Kit

K-886 Under-mount Install Kit



## Codes/Standards

ASME A112.19.7/CSA B45.10

CSA B45.5/IAPMO Z124

ASTM E162

ASTM E662

UL 1795

CSA C22.2 No. 218.2

Greenguard UL 2818 - Gold

CARB P2

## KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

## Available Color/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	0	
	96	
	47	
	NY	
	95	
	G9	
	33	
	K4	
	58	
	7	

USA/Canada: 1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com).



6-8-2017 12:53

THE BOLD LOOK  
OF **KOHLER**®




# Underscore® 6' BubbleMassage™ Bath K-5718-G

No change in measurements if connected with drain illustrated. (K-7272)



**Faucet Hole Locations  
(For KOHLER® Brand Only)**

Blower/Control Access  
34" (864 mm) W x  
15" (381 mm) H



## Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI) or Residual Current Device (RCD).

Blower: 240 V, 15 A, 50/60 Hz

## Technical Information

All product dimensions are nominal.

Installation: Drop-in, Under-mount  
Drain location: Center  
Basin area, bottom: 46-5/16" x 31-3/16" (1177 mm x 792 mm)  
Basin area, top: 63-7/16" x 34-1/4" (1611 mm x 869 mm)  
Weight: 130 lbs (59 kg)  
Minimum floor load: 53.4 lbs/ft² (260.7 kg/m²)  
Water depth: 18-5/8" (472 mm)  
Water capacity: 112.2 gal (424.7 L)  
Template: Drop-in, 1268440-7, required, included  
Electrical component rating: Blower: 240 V, 15 A, 50/60 Hz, 300 W

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Do not relocate or alter the PVC tee or coiled flexible tubing connected to the blower. Follow the blower relocation instructions exactly.